



LED Filament Pygmy E14



Product Overview

LED Filament Lamps operate direct from the mains, without the need for a transformer. making them quick and easy to install, simple to operate and lowering installation and user costs.

Features

- More eco-valued.
- Excellent color rendering and consistency
- Reliable construction

Safety and Maintenance

- Switch off supply before installing or removing lamp.
- Allow to cool before handling.
- Do not use in application where voltage is unable
- This is a glass product, handle with care

Specifications – E14 (boxed), E14 (blister 2pk)

SKU	S13561	S13562
Lamp	E14	E14
Nominal Power (W)	2W	2W
Voltage	220-240Vac 50Hz	220-240Vac 50Hz
Nominal Luminous Flux (lm)	240	240
CCT (K)	3000K warm White	3000K warm White
Nominal Lifetime (h)	15000	15000
Dimmable	No	No
Switching Cycles	15000	15000
Warm-up time to 60% (S)	instant	instant
Length (mm)	60	60
Diameter (mm)	26	26
Mercury (mg)	0	0
Clean-up instructions	See website	See website
Retrofit Yes		
Equivalent Wattage (W)	20	20
Rated Power (W)	2	2
Rated Luminous Flux (lm)	240	240
Rated Lifetime (h)	15000	15000
Power Factor	>0.4	>0.4
Rated Peak Candelas (cd)		
Lumen Maintenance Factor at		
Nominal Lifetime	15000	15000
CRI	>80	>80
Start Time (s)	instant	instant
Ambient Temperature Range (°C)	-20 to 40	-20 to 40

Energy Label – E14 (boxed), E14 (blister 2pk)


Energy Class	A++	A++
Energy Consumption (kWh/1000h)	2.00 (2)*	2.00 (2)*

* The kWh/1000h value published on the energy label is required to be rounded up to an integer according to the EU implementing directive on Energy Labelling. The value to 2 decimal places is given for reference

Product Markings – E14 (boxed), E14 (blister 2pk)

Voltage	220-240Vac 50Hz	220-240Vac 50Hz
Nominal Power (W)	2	2
Current (mA)		
CE Mark	Yes	Yes
WEEE Mark	Yes	Yes
Batch Code	Yes	Yes

Dimensions



Photometric Information

3000K

