

Portable Thermocouple Temperature Controller

CN-TOT





- ✓ Portable, Plug and Play
- ✓ Easy-to-Use Digital On/Off Controller
- ✓ Type J Thermocouple Mini Connector Input
- ✓ 5°C (9°F) Differential
- ✓ Audible Alarm
- ✓ Operating Exposure Temperature -10 to 55°C (-14 to 131°F)
- ✓ 1.8 m (6') Input Power Cord with Standard Plug (120 Vac, NEMA 5-15; 240 Vac, NEMA 6-15)
- ✓ Output Receptacle (120 Vac, NEMA 5-15R; 240 Vac, NEMA 6-15R)
- ✓ Average Accuracy of ±1% FS
- ✓ 120 or 240 Vac
- ✓ 15 A Capacity
- ✓ For Indoor Use

The CN-TOT portable thermocouple temperature controller is designed for indoor, general purpose use. It can control the temperature of small tanks, drums, pipes, intermediate bulk containers (IBCs), and other objects that require automatic control.



CN-TOT-A-175JF-120V shown smaller than actual size.



To Order

Model No.	Description
CN-TOT-A-175JF-120V	Controller, 10 to 79°C (50 to 175°F) range, 120V, 15 A
CN-TOT-A-175JF-240V	Controller, 10 to 79°C (50 to 175°F) range, 240V, 15 A

Ordering Example: CN-TOT-A-175JF-120V, thermocouple temperature controller, 10 to 79°C (50 to 175°F) range, 120V, 15 A.