

## 2W/10dB RF Fixed Attenuator, N Male to N Female Brass Nickel Body Up to 3 GHz



### **RF Fixed Attenuators Technical Data Sheet**

LCAT1003-10

#### **Features**

- N-Type connector interface
- DC to 3 GHz Frequency Range

### Applications

- Instrumentation
- · RF test systems
- · Prototyping and characterization

- Max Power 2 Watt (CW)
- VSWR < 1.2:1</li>
- Production systems
- Precision measurements

### **Description**

L-com carries a wide range of fixed attenuators with a broad selection of attenuation levels and frequency ranges. RF fixed attenuators lower the amplitude of a signal (attenuate) by specific amount and can be used in a wide variety of applications. These attenuators are used when signal levels need to be reduced to protect measurement equipment or other circuitry, to extend the range of power meters and amplifiers, and to impedance match circuits by reducing the VSWR seen by adjacent components. RF attenuators can prevent signal overload in amplifiers, receivers and detectors, adjusting the signal level to optimal power range.

Few RF components are as commonly used as fixed coaxial attenuators, and L-com carries one of the largest in-stock varieties and ships them same day. The 10 dB Fixed Attenuator LCAT1003-10 is rated to 2 Watts and operates from DC to 3 GHz. The versatile coaxial package uses type N male to type N female connectors and is also RoHS compliant.

#### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC	T V	3	GHz
Impedance		50		Ohms
Nominal Attenuation		10		dB
Attenuation Accuracy		0.5		dB
VSWR			1.2:1	
Input Power, Peak			500	Watts
5µs pulse with	0.5% duty cycle			
Input Power, CW		<del>-</del>	2	Watts
0.5W @ 125°C				

#### **Mechanical Specifications**

Size

 Length
 2.7559 in [70 mm]

 Width/Diameter
 0.7874 in [20 mm]

 Weight
 0.1543 lbs [69.99 g]

 Body Material and Plating
 Brass, Nickel

Configuration

Design Fixed

L-com, Inc. • 50 High St., West Mill, 3rd Floor, Suite #30 North Andover, MA 01845 © 2019 L-com, Inc. All Right Reserved



# 2W/10dB RF Fixed Attenuator, N Male to N Female Brass Nickel Body Up to 3 GHz



### **RF Fixed Attenuators Technical Data Sheet**

#### LCAT1003-10

#### Connectors

Description	Connector 1	Connector 2	
Туре	N Male	N Female	
Contact Material and Plating	Brass, Gold	Beryllium Copper, Gold	
Outer Conductor Material and Plating	Brass, Nickel	Brass, Nickel	
Body Material and Plating	Brass, Nickel	Brass, Nickel	

#### **Environmental Specifications**

**Temperature** 

**Operating Range** 

-55 to +125 deg C

#### **Compliance Certifications**

#### **Plotted and Other Data**

Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part

described herein for any particular purpose, and L-com does not assume any liability arising out of the use of any part or documentation.

## LCAT1003-10 CAD Drawing 2W/10dB RF Fixed Attenuator, N Male to N Female Brass Nickel Body Up to 3 GHz

