

CyberPower

CP600LCD Intelligent LCD UPS

Offering significant energy savings, battery backup and surge protection.



A compact UPS with standby topology, the CyberPower Intelligent LCD CP600LCD provides battery backup (using simulated sine wave output) and surge protection for desktop computers, workstations, networking devices, and home entertainment systems. During longer power outages, the CP600LCD delivers enough battery backup power to perform a graceful shutdown to protect against the loss of data and damage to valuable electronics. The multifunction LCD provides real time status and alerts of potential problems. The CP600LCD comes with a three-year warranty and a \$175,000 Connected Equipment Guarantee.

TYPICAL APPLICATIONS

- Desktop Computers
- Home Networking
- Home Theater Equipment
- Personal Electronics

FEATURES

- 600 VA / 340 W
- 8 Standard Outlets
- Standby Topology
- Full-time Surge Protection and Battery Backup
- Three-Year Warranty

SPECIFICATIONS

General		Output	
UPS Topology	Standby	VA	600 VA
Energy Star Certified	Yes	Watts	340 W
Input		Automatic Voltage Regulation	No
Frequency Range	57 - 63 Hz	On Battery Voltage	120 VAC \pm 5%
Plug Type	NEMA 5-15P	On Battery Frequency	60 Hz \pm 1%
Plug Style	Right Angle, 45° Offset Right	On Battery Waveform	Simulated Sine Wave
Cord Length (ft)	6 ft	Outlet Type	NEMA 5-15R
		Outlets - Total	8
		Outlets - Battery & Surge Protected	4
		Outlets - Surge-Only Protected	4
		Outlets - Transformer-Spaced	4
		Overload Protection	Internal Circuitry Limiting
		Transfer Time	4 ms

CP600LCD Intelligent LCD UPS



SPECIFICATIONS CONT.

Battery

Runtime at Half Load (min)	13
Runtime at Full Load (min)	2
Battery Type	Sealed Lead-Acid
Battery Size	12V/7Ah
Battery Quantity	1
User Replaceable	Yes
Replacement Battery Cartridge	RB1270B
Replacement Battery Cartridge Quantity	1
Typical Recharge Time	8 hours

Surge Protection & Filtering

Surge Suppression	1,030 J
EMI/RFI Filtration	Yes

Management & Communications

Multifunction LCD Panel	Displays: Current/Load Level, Runtime, Battery Level, Input Voltage, Output Voltage, Battery In Use, Overload, Silent Mode, Normal Mode
LED Indicators	Power On, Wiring Fault
Audible Alarms	On Battery, Low Battery, Overload, Fault
HID Compliant USB Port	Yes
Serial Port	Yes
Software	PowerPanel® Personal

Physical

Form Factor	Compact
Color	Black
Keyhole Mounting Slots	Yes
Dimensions - WxHxD (in)	11 x 6.8 x 3.5
Weight (lbs)	10.69

Environmental

Operating Temperature	32 °F to 95 °F / 0 °C to 35 °C
Operating Relative Humidity	0 - 95% (non-condensing)

Certifications

Safety	UL1778 cUL 107.3 FCC DOC Class B
Environmental	RoHS Compliant

Warranty

Product Warranty	3 Years Limited
Connected Equipment Guarantee	Lifetime
CEG Amount	\$175,000