




Features:

- Glass passivated chip junction in moulded plastic package
- 1,500W surge capability at 1ms
- Low zener impedance
- Excellent clamping capability
- Fast response time: Typically less than 1 ps from 0 volts to BV minimum
- Typical IR less than 1µA above 10V
- High temperature soldering: 260°C / 10 seconds / .375 inches, (9.5mm) lead length / 5 lbs. (2.3 kg) tension
- Low clamping voltage
- Wide voltage range
- High transient power dissipation
- No wear-out limitation
- Small physical size

Dimensions: 1.5KE Series



Dimensions : Inches (Millimetres)

Mechanical Data

Case : JEDEC DO-201AE moulded plastic
 Terminals : Axial leads, solderable per MIL-STD-202, Method 208
 Polarity : Colour band denotes cathode except in Bi-Directional
 Mounting Position : Any
 Weight : 0.045 ounce, 1.2 g

Maximum Ratings and Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified

Ratings	Symbol	Value 1.5KE Series	Units
Peak Power Dissipation at $T_A = 25^\circ\text{C}$, $TP = 1\text{ ms}$ (Note 1)	PPK	Minimum 1,500	Watt
Steady State Power Dissipation at $T_L = 75^\circ\text{C}$ Lead Lengths 5.8 to 7.6, 7.2 to 9.5 (Note 2)	P_D	5	
Peak Forward Surge Current, 8.3 ms Single Half Sine-Wave Superimposed on Rated Load (JECED Method) (Note 3)	I_{FSM}	200	Ampere
Operating and Storage Temperature Range	T_J, T_{STG}	-65 to +175	°C

Notes

1. Non-repetitive current pulse, per Fig. 3 and derated above $T_A = 25^\circ\text{C}$ per Fig. 2
2. Mounted on copper Leaf area of 0.79in² (20mm²)
3. 8.3 ms single half sine-wave, duty cycle = 4 pulses per minutes maximum

Rating and Characteristic Curves

1.5KE Series




Fig. 1-Peak Pulse Power Rating Curve




Fig. 3-Pulse Waveform




Fig. 5-Steady State Power Derating Curve




Fig. 2-Pulse Derating Curve




Fig. 4-Typical Junction Capacitance Unidirectional




Fig. 6-Maximum Non-Repetitive Peak Forward Surge Current Unidirectional

Transient Voltage Suppressors **multicomp** PRO

Uni-Directional 1,500 Watt Axial Lead TVS

Stand-off Voltage V_{rm} (V)	Breakdown Voltage V_{br} (V) Minimum	Breakdown Voltage V_{br} (V) Maximum	I_{test} (mA)	Clamping Voltage V_{clamp} A	Maximum Peak Pulse Current I_{pp} (A)	P_{tot} at $T_L = 75^\circ C$ (W)	Uni-Directional Part Number
5.5	6.45	7.14	10	10.5	143	5	1.5KE6.8A+
13.6	15.2	16.8		22.5	67		1.5KE16A+
15.3	17.1	18.9		25.2	59.5		1.5KE18A+
23.1	25.7	28.4		37.5	40		1.5KE27A+
25.6	28.5	31.5		41.4	36		1.5KE30A+
30.8	34.2	37.8		49.9	30		1.5KE36A+
40.2	44.7	49.4		64.8	23.2		1.5KE47A+
136	152	162		219	6.8		1.5KE160A+
342	380	420		548	4		1.5KE400A+

Bi-Directional 1,500 Watt Axial Lead TVS

Stand-off Voltage V_{rm} (V)	Breakdown Voltage V_{br} (V) Minimum	Breakdown Voltage V_{br} (V) Maximum	I_{test} (mA)	Clamping Voltage V_{clamp} A	Maximum Peak Pulse Current I_{pp} (A)	P_{tot} at $T_L = 75^\circ C$ (W)	Bi-Directional Part Number
5.8	6.45	7.14	10	10.5	143	5	1.5KE6.8CA+
13.6	15.2	16.8		22.5	67		1.5KE16CA+
15.3	17.1	18.9		25.2	59.5		1.5KE18CA+
23.1	25.7	28.4		37.5	40		1.5KE27CA+
25.6	28.5	31.5		41.4	36		1.5KE30CA+
28.2	31.4	34.7		45.7	33		1.5KE33CA+
30.8	34.2	37.8		49.9	30		1.5KE36CA+
40.2	44.7	49.4		64.8	23.2		1.5KE47CA+
136	152	168		219	6.8		1.5KE160CA+
342	380	420	548	4	1.5KE400CA+		

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

multicomp PRO