




5x20mm semi-enclosed PCB mounting 15mm pitch fuseholders

Product overview

- PCB mounting
- Fuse retaining insulation cover
- Enclosed contacts
- 15mm pitch
- Moulded in green UL94-V0 flame retardant PA
- EN60127
-     approved

PART NO.	TYPE
CFH17S	With spigot
CFH17	No spigot


SPECIFICATION	
Rating	6.3A/ 250V
Contacts/resistance	Tinned, nickel plated Brass, <math><5m\Omega</math>
Moulding	UL94-V0 flame retardant PA
Dielectric strength	3kV / 60"
Power dissipation	1.6W
Recommended PCB hole size	1.5mm
Insulation resistance	100M Ω
Operating temperature	-30°C to +85°C



5x20mm semi-enclosed PCB mounting 22.6mm pitch fuseholders

Product overview

- PCB mounting
- Fuse retaining insulation cover
- Enclosed contacts
- 22.6mm pitch
- Moulded in UL94-V0 flame retardant PA
- EN60127
-     approved



SPECIFICATION	
Rating	6.3A/ 250V
Contacts/resistance	Tinned, nickel plated brass, <math><5m\Omega</math>
Moulding	UL94-V0 flame retardant PA
Dielectric strength	3kV / 60"
Power dissipation	1.6W
Recommended PCB hole size	1.5mm
Insulation resistance	100M Ω
Operating temperature	-30°C to +85°C

PART NO.	TYPE
CFH14	No spigot
CFH14HB	Cover (black)

