


Screwless Terminal Blocks


- 1-36 poles 5, 5.08mm pitch
- 1-24 poles 7.5, 7.62mm pitch
- 1-18 poles 10, 10.16mm pitch
- Easily breakable to desired number of poles, end walls available on request
- Moulded in grey UL94-V0 flame retardant PA
- 0.5-1.5mm² (30-16AWG) solid & stranded cable
- Guided pin alignment
- Anti solder wicking
- Spacers in 2.5, 2.54, 5 & 5.08mm available
- Full customisation, produced from 1 pole units which can be pre-assembled to individual requirements
- Available without actuators (screwdriver operation) add suffix /W
-  approved

SPECIFICATION	5mm, 5.08mm	7.5mm, 7.62mm	10mm, 10.16mm
Rating	10A/250V	10A/500V	10A/630V
UL	10A/300V	10A/300V	10A/300V
VDE&IMQ	10A/250V	10A/750V	10A/750V
Dielectric strength	≥2kV	≥2.5kV	≥3kV
Impulse withstand voltage	4kV	6kV	6kV
Working temperature	110°C		
Moulding	UL94-V0 flame retardant PA		
Pin/terminal	Copper alloy, Ni & Sn		
Rising Clamp	Inox steel		
Recommended PCB hole	ø1.1mm		

5mm

5mm

TYPE NO.	POLES	LENGTH
CSTBV1/1	1	6.5mm
CSTBV1/2	2	11.5mm
CSTBV1/3	3	16.5mm
CSTBV1/4	4	21.5mm
CSTBV1/5	5	26.5mm
CSTBV1/6	6	31.5mm
CSTBV1/7	7	36.5mm
CSTBV1/8	8	41.5mm
CSTBV1/9	9	46.5mm
CSTBV1/10	10	51.5mm
CSTBV1/11	11	56.5mm
CSTBV1/12	12	61.5mm
CSTBV1/36	36	181.5mm



PCB
TERMINAL
BLOCKS

INTER-
CONNECTION

FUSES &
FUSE-
HOLDERS

LEDs &
INDICATORS

MINIATURE
SWITCHES

LIMIT &
SAFETY
SWITCHES

CONTROL
PRODUCTS

INTERFACE
MODULES &
SUPPORTS

RELAY
BASES

DIN RAIL
ENCLOSURES

BATTERIES

SOLAR
PANELS

TRANS-
FORMERS