



# 12Vmax Multi Tool CXT

## TM30DZ

Model TM30D is a cordless multi tool powered by 12V max slide Li-ion battery

10.8V Multi Tool CXT



### TECHNICAL SPECIFICATIONS

Battery Type	Lithium-ion
Body only machine	✓
Battery Quantity (2.0Ah)	0
Voltage	12 v
Shank	OIS
Oscillation Angle	3.2 °
Oscillations per Minute	6,000 - 20,000
Noise sound pressure	82 dB(A)
Noise sound power	93 dB(A)
Noise K factor	3 dB(A)
Vibration K factor	1.5 m/sec <sup>2</sup>
Vibration: Sanding	2.5 m/sec <sup>2</sup>
Vibration: Plunge Saw Blade	10.5 m/sec <sup>2</sup>
Net weight	1.1 - 1.3 kg

### USER BENEFITS

- Variable speed control dial.
- Soft start
- Anti-restart function.
- LED job light
- Accessories can be installed at 30° increments, across 360°
- Ergonomically best possible barrel grip, with a perfect circumference size and shape which fits the hand for extra comfortable handling.
- On-tool storage for hex wrench.
- Connectable to dust extractor with correct attachment

[Link to product - www.makita.com](http://www.makita.com)



# RELATED PRODUCTS

(Recom

## ■ OTHER