

# 18Vx2 Cordless or Corded L-Class Dust Extractor

## DVC151LZ

DVC151L is a corded and cordless vacuum cleaner powered by either AC mains power or two 18V LXT batteries in series.

**Class L - Removes 99.0% of dust with limit value for occupational exposure >1.0mg/m<sup>3</sup>**

Suitable for processes involving mica, china clay, gypsum.



### TECHNICAL SPECIFICATIONS

Max Air Flow (AC)	3.6 m <sup>3</sup> /min
Max Air Flow (DC)	2.1 m <sup>3</sup> /min
Max Sealed Suction (AC)	24 kPa
Max Sealed Suction (DC)	9 kPa
Suction Power (AC)	320 W
Suction Power (DC)	70 W
Battery Type	Lithium-ion
Body only machine	✓
Voltage	36 (18x2) v
Tank Capacity	15 litres
Noise sound pressure	75 dB(A)
Noise K factor	2.5 dB(A)
Input Wattage	1050 w
Vibration K factor	1.5 m/sec <sup>2</sup>
Vibration no load	2.5 m/sec <sup>2</sup>
Net weight	9.6 - 10.3 kg

### USER BENEFITS

- Dry type dust extractor
- Variable suction power by dial
- Double Insulation
- Operable by both AC and DC - AC takes priority if both are connected
- Large On/Off switch
- Battery cover
- HEPA filter with high filtration capacity for clean exhaust air.
- Removable storage box
- Removable power supply cord
- Large bumper protects walls and furniture from bumps and scratches.
- Caster stopper prevents the cleaner from moving unintentionally.
- Compatible with commercial plastic bags
- 5.0m power cord
- Automatic Self-cleaning Filter

Link to product - [www.makitauk.com](http://www.makitauk.com)



# RELATED PRODUCTS

(Recon

## ■ OTHER