

# K1H014Q

body for stepping switch - 2-pole - 45° - 12 A - for Ø 22 mm



## Main

|                                             |                                     |
|---------------------------------------------|-------------------------------------|
| Range of product                            | Harmony K                           |
| Product or component type                   | Cam switch body                     |
| Component name                              | K1                                  |
| [Ith] conventional free air thermal current | 12 A                                |
| Sub-assembly composition                    | Contact blocks + fixing plate       |
| Cam switch function                         | Stepping switch                     |
| Off position                                | With Off position                   |
| Poles description                           | 2P                                  |
| Switching positions                         | Right: 0° - 45° - 90° - 135° - 180° |
| Mounting location                           | Front                               |
| Fixing mode                                 | Ø 22 mm hole                        |
| Bezel material                              | Plastic                             |

## Complementary

|                                              |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
|----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Number of steps                              | 4                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Switching angle                              | 45 °                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| [Ui] rated insulation voltage                | 690 V degree of pollution 3 conforming to IEC 60947-1                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| [Ithe] conventional enclosed thermal current | 10 A                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| Rated operational power in W                 | 600 W AC-3 / 230 V 1 phase conforming to IEC 947-3<br>1500 W AC-3 / 400 V 1 phase conforming to IEC 947-3<br>1100 W AC-3 / 230 V 3 phases conforming to IEC 947-3<br>8300 W AC-21 / 400 V 3 phases conforming to IEC 947-3<br>1500 W AC-3 / 690 V 3 phases conforming to IEC 947-3<br>2200 W AC-23A / 400 V 3 phases conforming to IEC 947-3<br>1500 W AC-3 / 500 V 3 phases conforming to IEC 947-3<br>2200 W AC-23A / 500 V 3 phases conforming to IEC 947-3<br>1500 W AC-3 / 400 V 3 phases conforming to IEC 947-3<br>1500 W AC-23A / 230 V 3 phases conforming to IEC 947-3<br>2200 W AC-23A / 690 V 3 phases conforming to IEC 947-3<br>4800 W AC-21 / 230 V 3 phases conforming to IEC 947-3<br>10500 W AC-21 / 500 - 660 V 3 phases conforming to IEC 947-3 |
| [Ie] rated operational current AC            | 1 A at 500 V AC-15 conforming to IEC 947-5-1<br>2 A at 400 V AC-15 conforming to IEC 947-5-1<br>3 A at 230 V AC-15 conforming to IEC 947-5-1<br>1.8 A at 690 V AC-3 3 phases conforming to IEC 947-3<br>2.8 A at 500 V AC-3 3 phases conforming to IEC 947-3<br>2.8 A at 690 V AC-23A 3 phases conforming to IEC 947-3<br>3.3 A at 400 V AC-3 3 phases conforming to IEC 947-3<br>3.8 A at 500 V AC-23A 3 phases conforming to IEC 947-3<br>4.6 A at 230 V AC-3 3 phases conforming to IEC 947-3<br>4.8 A at 400 V AC-23A 3 phases conforming to IEC 947-3<br>5.6 A at 230 V AC-23A 3 phases conforming to IEC 947-3                                                                                                                                                |
| Electrical durability                        | 1000000 cycles AC-15<br>1000000 cycles AC-21<br>500000 cycles AC-23<br>500000 cycles AC-3                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| Operating rate                               | 2.5 cyc/mn AC-21<br>2.5 cyc/mn AC-23<br>2.5 cyc/mn AC-3<br>8.333 cyc/mn AC-15                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| Short-circuit current                        | 10000 A                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Short-circuit protection                     | 16 A by cartridge fuse, type gG                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| [Uimp] rated impulse withstand voltage       | 4 kV in isolating function<br>6 kV conforming to IEC 947-1                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| Contact operation                            | Slow-break                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

|                       |                                                                                                                                 |
|-----------------------|---------------------------------------------------------------------------------------------------------------------------------|
| Positive opening      | With                                                                                                                            |
| Electrical connection | Captive screw clamp terminals flexible, 2 x 1.5 mm <sup>2</sup><br>Captive screw clamp terminals solid, 1 x 2.5 mm <sup>2</sup> |
| Mechanical durability | 1000000 cycles                                                                                                                  |
| Product weight        | 0.165 kg                                                                                                                        |

### Environment


|                                       |                                                                                                                               |
|---------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| standards                             | CENELEC EN 50013<br>EN/IEC 60947-3 for power circuit<br>EN/IEC 60947-5-1 for control circuit                                  |
| product certifications                | CSA 240 V 1 hp 1 phase<br>CSA 240 V 3 hp 3 phases 2 -pole(s)<br>UL 240 V 1 hp 3 phases<br>UL 240 V 0.33 hp 1 phase 2 -pole(s) |
| protective treatment                  | TC                                                                                                                            |
| ambient air temperature for operation | -25...55 °C                                                                                                                   |
| ambient air temperature for storage   | -40...70 °C                                                                                                                   |
| shock resistance                      | 30 gn conforming to IEC 68-2-27                                                                                               |
| vibration resistance                  | 5 gn, 10...150 Hz conforming to IEC 68-2-6                                                                                    |

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

### Body with Plastic Base

#### Front Mounting by Ø 22 mm/0.87 in. Hole




a2 79 mm/3.11 in.


### Link Positions (Factory Mounted)

#### Diagram for 2 to 6-step Stepping Switches

Select the number of steps according to the product characteristics.




### Angular Position of Switch



### Switching Program

#### Diagram for 2 to 6-step Stepping Switches

Select the number of steps according to the product characteristics.



### Convention Used for Switching Program Representation

-  Contact closed
-  Contact closed in 2 positions and maintained between the 2 positions
-  Sealed assembly for auto-maintain control
-  Overlapping contacts
-  Spring return position: for a switching angle of 90°, spring return is over 30° after the last position (for a maximum of 3 simultaneous contacts).

Example:

