



Main

| | |
|-------------------------------|--|
| Range of product | OsiSense XC |
| Series name | Standard format |
| Product or component type | Limit switch body |
| Device short name | ZCKM |
| Body type | Fixed |
| Product compatibility | XCKM |
| Associated head | ZCKD02 ZCKD05 ZCKD06 ZCKD08 ZCKD10 ZCKD109 ZCKD15 ZCKD16 ZCKD17 ZCKD21 ZCKD219 ZCKD23 ZCKD239 ZCKD41 ZCKD59 ZCKD81 ZCKD91 ZCKD029 |
| Body material | Metal |
| Cable entry | 3 entries tapped for M20 x 1.5 cable gland |
| Number of poles | 2 |
| Contacts type and composition | 2 NC |
| Contact operation | Snap action |
| Number of steps | 1 1 position |
| Contacts material | Silver plated contacts |

Complementary

| | |
|---|--|
| Local display | Without |
| Electrical connection | Screw-clamp terminals, clamping capacity: 1 x 0.34...2 x 1.5 mm ² |
| Positive opening | With |
| Minimum actuation speed | 0.01 m/min |
| [I _e] rated operational current | 3 A at 240 V, AC-15, A300 conforming to EN/IEC 60947-5-1 appendix A 0.27 A at 250 V, DC-13, Q300 conforming to EN/IEC 60947-5-1 appendix A |
| [I _{the}] conventional enclosed thermal current | 10 A |
| [U _i] rated insulation voltage | 300 V conforming to UL 508 contact block 500 V degree of pollution 3 conforming to IEC 60947-1 contact block 300 V conforming to CSA C22.2 No 14 contact block |
| Resistance across terminals | 0.25 mOhm conforming to IEC 60255-7 category 3 |
| [U _{imp}] rated impulse withstand voltage | 4 kV conforming to IEC 60664 4 kV conforming to IEC 60947-1 |
| Short-circuit protection | 6 A by gG cartridge fuse |
| Electrical durability | 5000000 cycles, DC-13 120 V, 2 W, operating rate: < 60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 5000000 cycles, DC-13 24 V, 4 W, operating rate: < 60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 5000000 cycles, DC-13 48 V, 3 W, operating rate: < 60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C |
| Width | 64 mm |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

| | |
|-------------------------------|-------------------------------------|
| Height | 64 mm |
| Depth | 30 mm |
| Product weight | 0.21 kg |
| Terminals description ISO n°1 | (13-14)NO (21-22)NC (31-32)NC |

Environment

| | |
|---------------------------------------|--------------------------------------|
| IP degree of protection | IP66 |
| IK degree of protection | IK05 |
| ambient air temperature for operation | -25...70 °C for standard environment |
| ambient air temperature for storage | -40...70 °C |
| environmental characteristic | Standard environment |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 1005 - Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|