# 12V Alkaline Battery 55mAh, LR23A



# RoHS Compliant



# **Specifications**

Nominal Voltage : 12 Volts (Open circuit voltage 12 Volts +0.4/-0)

Nominal Capacity : 55mAh

(Test condition: 20kΩ Load, continuous discharge, end voltage of 6V)

Average Weight :  $8g \pm 0.2g$ Shelf Life : 24 Months

Heavy Metal Content : Mercury(Hg) content should be less than 2%

Cadmium (Cd) content should be less than 5 PPM Lead (Pb) content should be less than 5 PPM


Storage Temperature : Not more than +45°C Humidity : Not more than 75%

#### **Performance**


Discharges						
Test condition			Average Duration 1) at 20°C			
Load	Daily Period	End Voltage	Initial	After 12 months storage 2)	After 36 months storage 2)	
20kΩ	24 h/d	6V	110h	100h	88h	
1kΩ	24 h/d	6V	235 min.	175 min.	150 min.	

<sup>1)</sup> Average service life will be calculated without the highest and the lowest of 9 samples

# **Diagram**







# **Part Number Table**

Description	Part Number
Alkaline Battery, 12V, 55mAh, LR23A	PEL01228

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands



<sup>&</sup>lt;sup>2)</sup> Storage conditions: temperature 20+2°C and the Relative Humidity shall be 65+20%