



Main

Range of product	Zelio Count
Product or component type	Hour counter
Display type	Mechanical
Size	48 x 48 mm
Display digits	7 digit(s)
Reset	Without
Technology type	Electromechanical

Complementary

[Us] rated supply voltage	230 V AC (Us +/- 10 %) at 50 Hz
Power consumption in VA	1 VA
Backup time	Permanent
Counting mode	Adding 1/100 of an hour
Time range	0...99 999.99 h
Input function	Enable
Input type	Contact
Mounting mode	Flush-mounted
Mounting support	Panel mounting
Fixing mode	By self-locking clamp
Connections - terminals	Screw terminal block
Height	48 mm
Product weight	0.06 kg
Width	48 mm
Character size	5 mm
CAD overall width	48 mm
CAD overall height	48 mm
CAD overall depth	63 mm

Environment

Standards	EN/IEC 50081-2 EN/IEC 50082-2
-----------	----------------------------------

VDE 0435

Product certifications	UR
Ambient air temperature for operation	-10...50 °C
Ambient air temperature for storage	-25...70 °C
Vibration resistance	3 gn (f = 10...150 Hz) conforming to EN/IEC 60068-2-6
Shock resistance	30 gn for 11 ms conforming to EN/IEC 60068-2-27
Electrical shock protection class	Class II conforming to EN/IEC 60536


Contractual warranty

Warranty period	18 months
-----------------	-----------


Electromechanical and Electronic Totalizing Timers

Timers with Mechanical Display

XBKH7000000•M




Flush-Mounting



Timers with LCD Display

XBKH81000033E



Flush-Mounting

