



Product Data Sheet

www.brannan.co.uk

Mini Thermo-Anemometer

Easy to use windspeed meter as part of our range of mini environmental meters.

Product Features

- Air velocity measurement
- User selectable units: m/s, ft/min, Km/h, MPH, Knots
- MAX/MIN record and data hold function
- Large backlit colour LCD
- Low battery indicator
- Auto power off - enable/disable function
- Supplied with 3 point Calibration Certificate
- CE & RoHS/WEEE Compliant

Product Specifications

Measurement	Range	Accuracy	Resolution
Air Velocity:	0.4 to 30 m/s	+/- 3% or 0.3 m/s	0.1 m/s
	1.4 to 108 Km/hr	+/- 3% or 1.0 Km/hr	0.1 Km/hr
	0.9 to 67 MPH	+/- 3% or 0.4 MPH	0.1 MPH
	0.8 to 58 knots	+/- 3% or 0.4 knots	0.1 knots
	80 to 5900 ft/min	+/- 3% or 40 ft/min	1.0 ft/min
Temperature:	-20 to +70°C&F	+/- 1.5°C (2.7°F)	0.1°C&F
Data Update:	300 ms		
Power Off:	Auto shut down after 15 mins inactivity (except when auto off disabled)		
Operating Conditions:	-20 to +60°C&F / 10 to 90%RH		
Storage Conditions:	-20 to +60°C&F / 10 to 75%RH		
Battery:	3 x AAA (included) Average life - 60 hours on continuous use		
Dimensions:	LCD: 30 x 28mm		
	Net: 178.5 x 56 x 30.5mm		
	Gross: 247 x 130 x 40mm		
Weight:	Meter: 114.5g (including batteries)		
	Paper: 19g (card, instructions & certificate)		
	Blister: 35.5g		
	Gross: 169g		



Description	Barcode	Product No
Mini Thermo-Anemometer	5 011405 134707	13/470/0

PDS 0283:17:R2

Please note: all information on this data sheet is correct at the time of printing, but our policy is one of continuous product development. We reserve the right to change specification without notice.

