# Thermal Non-silicone Grease





## **Description**

This product is a high performance thermal interface non-silicone grease.

# RoHS Compliant

#### **Features**

- NO Low MW siloxane E, Siloxane Volatiles D4 to D20, 0%
- · Low contact resistance
- Bondline thickness of 30µm
- · Can be dispensed or screen and stencil machine printed
- · Exceptionally low thermal resistance
- No pump out of reliability issues
- · Ease of application and rework

# **Applications**

#### Displays, lighting protection

PDP TV, LCD CCFL and LCD LED display backlight, LED signage, projectors and new display technology.

#### Consumer and industrial electronics

Mobile telephone, communication base station, laptop, notebook, computer servers, handheld gaming devices, memory modules, CPU modules, amplifiers, batteries, and DC to DC converter power supplies.

#### **Automotive electronics**

Engine management, electronic suspension, braking systems, communication and multimedia systems, comfort convenience features, vehicle lighting, vehicle controls, hybrid vehicle battery thermal management, electric vehicle thermal management.

### **Properties**

Characteristic	Value	Test Method
Filler	Metal-filled	-
Viscosity	336	Pass
Density	2.6g/cm <sup>3</sup>	ASTM D792
Colour	Grey	-
Low MX Siloxane ppm	0	D4-D20
Outgassing (TML)	0.2%/Wt	ASTM E595
Outgassing (CVCM)	0.1%/Wt	ASTM E595
Thermal Conductivity	4Wm/K	ASTM D5470
Thermal Impedance	0.012°C mm <sup>2</sup> /W	ASTM D5470
Bond line Thickness	0.003mm	-
Dielectric Strength, kV/mm	NA	ASTM D149
Volume Resistivity	>108Ω-cm	ASTM D257
Operating Temperature Range	-50°C to +150°C	-

#### **Part Number Table**

Description	Part Number
Thermal Non-silicone Grease, Grey, 4W/mK, 30g	MPGCS-040-GNS-30g

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

