

Laser Distance Meter



Specifications:

Range	: 0.05m to 60m (0.15ft to 196.8ft)
Measuring Accuracy up to 10m	: Typ. $\pm 1.5\text{mm}$ ($\pm 0.06''$)
Measuring Units	: Meter, Inch, feet
Laser Class	: Class II
Laser Type	: 635nm, <1mW
Area, Volume Calculations	: Yes
Indirect Measurement using Pythagoras	: Yes
Addition / Subtraction	: Yes
Continuous Measurement	: Yes
Min/Max Distance Tracking	: Yes
Display Illumination & Multi-Line Display	: Yes
Beep Indication	: Yes
Dust Protect / Splash Proof	: IP54
History Measurement Records	: 20
Keyboard Type	: Super Soft-Touch (Long Life)
Operating Temperature	: 0°C to 40°C (32°F to 104°F)
Storage Temperature	: -10°C to 60°C (14°F to 140°F)
Battery Life	: Up to 4,000 Measurements
Batteries	: Type AAA 2 × 1.5V (Not Included)
Auto Laser Switch-Off	: After 0.5min
Auto Instrument Switch-Off	: After 3min
Dimension	: 110mm × 46mm × 28mm
Weight	: 135g

Part Number Table

Description	Part Number
Laser Distance Meter, 60m, Black	72-13595

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. TENMA is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
 Farnell.com/exclusive-brands
 Element14.com/exclusive-brands



Micromapper Kit



Features:

- Electronically locates cables, gas and water pipes
- Traces hidden ceiling joists and wall studding
- Senses presence of mains power without touching live wires
- Locates breaks in circuits and cables
- Identifies faulty plugs, switches and sockets
- Incorporates audio signal and indicator light

Specification:

Test Detector Type : Metal, Power, Stud

Part Number Table

Description	Part Number
Micromapper Kit	72-6792

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. TENMA is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

