



6W

VT-606SQ 6W LED PREMIUM PANEL WITH SAMSUNG CHIP
 COLORCODE:6400K SQUARE

Lumens 420	Beam Angle 120	Dimensions ?120x120x12mm
----------------------	--------------------------	------------------------------------

White
 SKU:705



Technical Information

Instant Start:	0-100% lt1Sec
Output Voltage:	DC:12-24V
Watts:	6
Lumens:	420
Shape:	Square
Beam Angle:	120
Cutting Size:	?110x110mm
Unit Color:	White
Body Type:	Aluminium
Long life:	20,000 Hours

LED Chip Type:	SMD
IP Rating:	IP20
Dimmable:	No
Warranty (Years):	5
PF:	>0.5
CRI:	>80
Operation Temperature:	-20°C to 45°C
Input Power:	AC:85-265V,50/60Hz
Sensor Compatibility:	Yes

Features

- ✓ Contemporary & Elegant Design
- ✓ Highly Efficient LED Samsung Chip
- ✓ Easy to install - Plug & Play
- ✓ High-quality power driver ensures a reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ No Lead or Mercury content hence Environment-friendly
- ✓ Easy to install & Low Maintenance
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs 0.2275

Unit CBM 0.000755

Listing Details

EAN Code 3800157641616

Commodity Code 9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton) 40

Qty Per Pallet 1600

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES