



**12W**

VT-612RD 12W LED PREMIUM PANEL WITH SAMSUNG CHIP  
 COLORCODE:4000K ROUND

Lumens <b>1000</b>	Beam Angle <b>120</b>	Dimensions <b>?170x12mm</b>
-----------------------	--------------------------	--------------------------------

Day White  
 SKU:713



## Technical Information

Output Voltage:	DC:24-48V	LED Chip Type:	SMD
Watts:	12	IP Rating:	IP20
Lumens:	1000	Dimmable:	No
Shape:	Round	Warranty (Years):	5
Beam Angle:	120	PF:	>0.6
Cutting Size:	?160mm	CRI:	>80
Unit Color:	White	Operation Temperature:	-20°C to 45°C
Body Type:	Aluminium	Input Power:	AC:85-265V,50/60Hz
Long life:	30,000 Hours	Sensor Compatibility:	Yes

## Features

- ✓ Contemporary & Elegant Design
- ✓ Highly Efficient LED Samsung Chip
- ✓ Easy to install - Plug & Play
- ✓ High-quality power driver ensures a reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ No Lead or Mercury content hence Environment-friendly
- ✓ Easy to install & Low Maintenance
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.325
Unit CBM	0.001368

### Listing Details

EAN Code	3800157641692
Commodity Code	9405403990

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	1000

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

**70**

COUNTRIES