

ESD Safe Soldering Station



Features

- HD LCD display
- 3 Programmable preset temperature buttons
- On / Off switch on side unit
- Dual wire ceramic heater
- Includes soldering iron, stand, sponge and power cord.



Technical Specifications

Power Consumption	: 60W
Input Voltage	: 220V AC \pm 10% 50Hz
Heater Voltage	: 24V AC
Temperature Range	: 150°C to 450°C (302°F to 842°F)
Temperature Stability	: \pm 2°C (still air, no load)
Temperature Accuracy	: \pm 15°C
Tip to Ground Impedance	: < 2 Ω
Tip to Ground Potential	: < 5mV
Dimension (L x W x H)	: 146mm x 120mm x 91mm
Weight	: 1.8kg

Part Number Table

Description	Part Number
Soldering Station, ESD Safe, 60W, 220V AC, 450°C Max. Temp., EU Plug	21-10115 EU
Soldering Station, ESD Safe, 60W, 220V AC, 450°C Max. Temp., UK Plug	21-10115 UK

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. TENMA is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands



Solder Smoke Absorber



RoHS
Compliant



Specifications

Voltage Rating : 220V AC to 240V AC 50Hz
 Power Consumption : 23W
 Absorption Capacity : 1M³/min(Max)
 Colour : Black

Specification Table

Part Number	ESD Safe	Plug Type	Standard Mount	Overall Dimension (mm)	Weight	Accessories
D00372	No	EU	Bench Top	200(W) × 270(H) × 168(D)	1400g	D00376 (2 pieces)
D00374	Yes		Table Clamp	-	-	D00376 (2 pieces) and Connector(2 pieces)
D00373	No			-	-	
D00375	Yes			-	-	

Part Number Table

Description	Part Number
Smoke Absorber, Bench Top	D00372
Smoke Absorber, Bench Mount	D00373
Smoke Absorber, Bench Top, ESD Safe	D00374
Smoke Absorber, Bench Mount, ESD Safe	D00375
Carbon Filter, Smoke Absorber	D00376

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. DURATOOL is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
 Farnell.com/exclusive-brands
 Element14.com/exclusive-brands

