

Han M23 06 Male - solder (termination)



Part number	09 15 106 2602
Specification	Han M23 06 Male - solder (termination)
HARTING eCatalogue	https://b2b.harting.com/09151062602

Identification

Category	Inserts
Series	Han® M23 Signal
Element	Inserts

Version

Termination method	Solder termination
Gender	Male
Number of contacts	6

Technical characteristics

Conductor cross-section	2.5 mm ² max.
Rated current	20 A
Rated voltage	300 V
Rated impulse voltage	2.5 kV
Pollution degree	3
Insulation resistance	> 10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (insert)	Polyamide
Colour (insert)	White
Material (contacts)	Copper alloy
Surface (contacts)	Gold plated



Pushing Performance

Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

Commercial data

Packaging size	5
Net weight	7.1 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440205 Contact insert for industrial connectors