

Han M23 male-c 1mm (0,14 – 1,00mm²) Au



| | |
|--------------------|---|
| Part number | 09 15 100 6102 |
| Specification | Han M23 male-c 1mm (0,14 – 1,00mm ²) Au |
| HARTING eCatalogue | https://b2b.harting.com/09151006102 |

Identification

| | |
|----------------------------|-----------------------------|
| Category | Contacts |
| Series | Han [®] M23 Signal |
| Type of contact | Crimp contact |
| Description of the contact | Turned 1 mm |

Version

| | |
|--------|------|
| Gender | Male |
|--------|------|

Technical characteristics

| | |
|-------------------------|----------------------------|
| Conductor cross-section | 0.14 ... 1 mm ² |
| Conductor cross-section | AWG 26 ... AWG 17 |
| Contact resistance | ≤3 mΩ |
| Stripping length | 4 mm |

Material properties

| | |
|-----------------------------|--|
| Material (contacts) | Copper alloy |
| Surface (contacts) | Gold plated |
| RoHS | compliant with exemption |
| RoHS exemptions | 6c: Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |

Specifications and approvals

| | |
|----------------|------------|
| Specifications | EN 60664-1 |
|----------------|------------|



Pushing Performance

Specifications and approvals

| | |
|--|-----------|
| | IEC 61984 |
|--|-----------|

Commercial data

| | |
|--------------------------------|----------|
| Packaging size | 100 |
| Net weight | 0.21 g |
| Country of origin | France |
| European customs tariff number | 85366990 |