

For over 45 years, **PANDUIT®** has been the world leader in the design and manufacture of wiring duct in a wide selection of sizes, styles, colors and materials. The **PANDUIT®** name has become synonymous with high quality, innovative wiring duct products used to route, protect and conceal wiring in a wide variety of industrial control and telecommunications applications. **PANDUIT®** continues to develop new wiring duct solutions to satisfy the wire management challenges facing our customers worldwide.


Wiring Duct Functional Part Number System Makes Ordering Easy

G	.5	X	.5	LG	6	-A
Type/Style	Nominal Width In. or mm		Nominal Height In. or mm	Color	Length Ft. or M	-A = Adhesive Backed = Without Adhesive (leave blank) NM = No Mounting Holes
G = Wide Finger Flush Design				LG = Light Gray		
F = Narrow Finger Flush Design				DG = Dark Gray		
FS = Solid Wall Flush Design				WH = White		
H = Wide Finger Hinged Design				BL = Black		
D = Round Hole Flush Design				IB = Intrinsic Blue		
NNC = Halogen Free Design				BR = Beige		
NE = <i>NORYL</i> * Wide Finger Design				IG = International Grey		
MC = Metric Narrow Finger Design						
TMC = Low Smoke Metric Design						

Note: See **page F12** for UL94 requirements.
**NORYL* is a registered trademark of General Electric Company.

Wiring Duct *Voice & Data*


PANDUCT® Type G — Wide Slot Wiring Duct



- Wide selection of sizes available in black color to compliment the look of telecommunications racks and hardware
- Made of rigid PVC
- UL Recognized continuous use temperature: 50°C (122°F)
- UL94 Flammability Rating of V-0
- Provided with mounting holes
- Conforms with NFPA 79-2002 section 14.3.1 requirement for flame retardant material



- nonmetallic, non-flame propagating CDS
- medium impact resistance
- 331 temperature classification
- cover removal without tools



Reference	Page(s)
Color Availability	F14
Adhesive Tape	E12, E13
Dimensions	F2
Wirefill Guide	F8
Material Specifications	F13
Tools & Accessories	D11, D12, Section E
Installation Tips	F15

Part Number	Duct Size W x H		Cover Part Number	Duct Std. Ctn. Qty.	Cover Std. Ctn. Qty.	Length (ft)
	In.	mm				
G.75X2BL6	.93 x 2.03	23.6 x 51.6	C.75BL6	120	120	6
G1X1BL6	1.26 x 1.12	32.0 x 28.4	C1BL6	120	120	6
G1X1.5BL6	1.26 x 1.62	32.0 x 41.1		120		
G1X2BL6	1.26 x 2.12	32.0 x 53.8		120		
G1X3BL6	1.26 x 3.12	32.0 x 79.2		120		
G1X4BL6	1.26 x 4.10	32.0 x 104.1		60		
G1.5X1.5BL6	1.75 x 1.62	44.5 x 41.1	C1.5BL6	120	120	6
G1.5X2BL6	1.75 x 2.12	44.5 x 53.8		120		
G1.5X3BL6	1.75 x 3.12	44.5 x 79.2		120		
G1.5X4BL6	1.75 x 4.10	44.5 x 104.1		60		
G2X1BL6	2.25 x 1.12	57.2 x 28.4	C2BL6	120	120	6
G2X2BL6	2.25 x 2.12	57.2 x 53.8		120		
G2X3BL6	2.25 x 3.12	57.2 x 79.2		60		
G2X4BL6	2.25 x 4.10	57.2 x 104.1		60		
G2.5X3BL6	2.75 x 3.12	69.9 x 79.2	C2.5BL6	120	120	6
G3X2BL6	3.25 x 2.12	82.6 x 53.8	C3BL6	120	120	6
G3X3BL6	3.25 x 3.12	82.6 x 79.2		60		
G3X4BL6	3.25 x 4.10	82.6 x 104.1		60		
G4X2BL6	4.25 x 2.12	108.0 x 53.8	C4BL6	60	120	6
G4X3BL6	4.25 x 3.12	108.0 x 79.2		60		
G4X4BL6	4.25 x 4.10	108.0 x 104.1		60		
G4X5BL6	4.25 x 5.10	108.0 x 129.5		60		

Part Number shown for BL (Black). For other color availability see Color Selection Guide, [page F14](#).