

THM
THM WO 17.8/34 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Similar to illustration

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Type	THM WO 17.8/34 WS
Order No.	1774380000
Version	THM, Conductor and cable markers, 4.4 - 6.7 mm, 17.8 x 33.9 mm, white
GTIN (EAN)	4032248148561
Qty.	1 pc(s).
compatible printer	2430920000 2448870000

**THM
THM WO 17.8/34 WS**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	33.9 mm	Width (inches)	1.335 inch
Height	17.8 mm	Height (inches)	0.701 inch
Depth	0.025 mm	Depth (inches)	0.001 inch
Net weight	388 g		

General data

Adhesive	Polyacrylate adhesive	Approval acc. to UL 969	Yes
Colour	white	Halogen	No
Material	Polyester film	Material colour according to resistance code	9
Number per roll	3,000	Operating temperature range	-40... 150 °C
Size of labelling field	13 x 17.8 mm	Type of printing	neutral
UL 94 flammability rating	V-0	Version	Self-adhesive
Width	33.9 mm		

Conductor and cable markers

Conductor O.D.	4.4 - 6.7 mm	Conductor O.D., max.	6.7 mm
Conductor O.D., min.	4.4 mm	Conductor cross-section, max.	35 mm ²
Conductor cross-section, min.	0.75 mm ²	Halogen	No

Classifications

ETIM 3.0	EC001530	ETIM 4.0	EC001288
ETIM 5.0	EC001530	ETIM 6.0	EC001530
UNSPSC	44-12-17-08	eClass 5.1	27-14-91-03
eClass 6.2	27-40-04-01	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-03	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

Approvals

ROHS	Conform
------	---------

Downloads


Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
Software	M-Print PRO configuration file

Data sheet

THM
THM WO 17.8/34 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings



Data sheet

**THM
THM WO 17.8/34 WS**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Accessories

Ink ribbons



Our marking systems can be used to quickly and reliably label connector markers, conductor and cable markers, device markers and labels. The M-Print® PRO software enables rapid and easy identification of your electrical equipment. You can design, label and order your marking materials professionally and quickly. Frames, barcodes, graphics or photos are easily incorporated. The versatile data conversion routines enable quick and flexible data integration. The Weidmüller PrintJet ADVANCED, MCP Plus and MCP Basic printers and the THM series printers are available for printing.

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
RIBBON MM 110/360 SW	2005070000	Ink ribbon	4050118390049	1 pc(s).