

Insulating Mastics

Plymouth

4000 PLYSEAL®-V Vinyl Reinforced Insulating Mastic

Cat.	Form	Dimensions	Packaging	Weight
2620	roll	4" x .133" x 10' 102mm x 3,4mm x 3m	10/case B	34 lbs 15 kg
2621	pad	4" x .133" x 4" 102mm x 3,4mm x 102mm	10 pads/bx, 10 bxs/case	11 lbs 5 kg
2622	pad	4" x .133" x 6 1/2" 102mm x 3,4mm x 165mm	10 pads/bx, 10 bxs/case	17 lbs 8 kg

5000 BUS-SEAL EPR-Backed Insulating Mastic

Cat.	Form	Dimensions	Packaging	Weight
8371	roll	4" x .155" x 10' 102mm x 3,9mm x 3m	10/case B	36 lbs 16 kg

RUBBER MASTIC (RM) Tapes

Cat.	Form	Dimensions	Packaging	Weight
2619	roll	1 1/2" x .065" x 10' 38mm x 1,65mm x 3m	30/case IB	38 lbs 18 kg
2625	roll	2" x .065" x 10' 51mm x 1,65mm x 3m	30/case B	30 lbs 14 kg
2719	roll	1" x .065" x 10' 25,4mm x 1,65mm x 3m	10/case B	5 lbs 2 kg

VINYL MASTIC (VM) Tapes

Cat.	Form	Dimensions	Packaging	Weight
2617	roll	3/4" x .025" x 20' 19mm x 0,635mm x 6m	80/case B	29 lbs 13 kg
2618	roll	1 1/2" x .025" x 20' 38mm x 0,635mm x 6m	40/case C	26 lbs 11 kg
2609	roll	4" x .050" x 10' 100mm x 1,3mm x 3m	10/case B	13 lbs 6 kg

WATERSEAL MASTIC

Cat.	Form	Dimensions	Packaging	Weight
2856	pad	2 1/2" x .125" x 2' 64mm x 3,2mm x 610mm	40 pads/case IB	17 lbs 8 kg

Low Voltage Splice Kits



SPLICE WRAP™ One-Step Splice Kit

For insulating and water-proofing direct burial or overhead splices and terminations through 2000V. For cable jacket repair and restoration, and ground seal for shielded power cable. Suitable for straight and branch joints. Easy 1-step application. Connectors not included.

SPLICEWRAP One-Step Splice Kit

Cat.	Range	Packaging	Weight
8910	up to 500 kCMIL	20/case B	6 lbs. 3 kg