



Multi-Tool

M9800KX2

Model M9800 is a Multi tool with excellent performance that has been developed from TM3000C



TECHNICAL SPECIFICATIONS

Oscillation Angle	3.2 °
Oscillations per Minute	15,000 - 22,000
Noise sound pressure	79 dB(A)
Noise K factor	3 dB(A)
Input Wattage	200 w
Vibration K factor	1.5 m/sec ²
Vibration: Sanding	2.5 m/sec ²
Vibration: Scraping	9.5 m/sec ²
Vibration: Plunge Saw Blade	8.0 m/sec ²
Vibration: Segmental Saw Blade	4.0 m/sec ²
Net weight	1.2 - 1.3 kg

USER BENEFITS

- Compact & Lightweight
- Variable speed
- Thumb On/Off switch, positioned for ease of use when holding body of machine.
- Hex wrench holder on body.
- Accessories can be installed at 30° increments, across 360°
- Uses OIS interface.
- Double Insulation

Link to product - www.makita.com



RELATED PRODUCTS

(Recom

■ OTHER