

WXP 65

Product no.: T0052921199N



Benefits

- › Intelligent soldering Iron 65 W, 24 V
- › For small and medium components with average energy demand
- › For fine solder jobs with WX stations
- › Parameter memory such as standby temperatures, automatic switch-off time
- › Reduces total costs of ownership due to motion sensor
- › Visual process control through LED signal function
- › Interchangeable XNT soldering tips at low cost prices
- › Power Response heating technology with improved sensor position
- › fast reaction time


For this purpose, we recommend:



Solder fume extractors



Pre-heating plates



Cleaning




Soldering tips



Technical Data

Active Tip heating element technology	---
Power Response heating element technology	on
Silver Line heating element technology	---
Voltage	24 V
Power	65 W
Tip range	XNT
Supply unit	---
WX-compatible	on
Temperature range °C	100 - 450
Temperature range °F	200 - 850
Heating time	7
Safety rest	WDH 10 (T0051512199)
Safety rest (optional)	WDH 10 (T0051512199)
Barrel	T0058765758, T0058765767
Integrated direct extraction	Attachment T0052918699 / T0052921499

Owning the bench



PROFESSIONAL



FILTRATION



EREM



XCELITE