






DESCO FLOOR MAT SELECTION CHART

FLAT MATS

Statfree	Image	Thickness	Material Construction	Resistance Classification (Rtt in ohms)	Surface	Best Application	Anti-Fatigue Properties	Use with a Rolling Chair or Cart	Special Lengths Can be cut or configured by End User
CV280		0.080"	Homogeneous polymer matrix of PVC	Conductive < 1×10^6	Pebble embossed	High traffic areas and good for use under chairs and carts	Minimal	Yes	Yes
G2		0.060"	Homogeneous rubber	Conductive < 1×10^6	Light Texture	Wave solder areas	Minimal	No	Yes

ANTI-FATIGUE

i		0.500"	Nitrile butadiene rubber	Conductive < 1×10^6	Air cell	Long term standing tasks	Best	No	No ²
DPL Plus¹		0.450"	Homogeneous Vinyl with anti-fatigue foam rubber bottom layer	Conductive < 1×10^6	Embossed diamond	Moderate term standing tasks	Better	Yes ³	No
S Plus		0.375"	Cross-link vinyl/nitrile rubber foam	Dissipative 1×10^6 to $< 1 \times 10^9$	Pebble finish embossed surface	Short term standing tasks	Good	No	No

1. Desco does not recommend cutting or altering these standard sized mats. However, Desco can manufacture these mats in custom sizes and configurations. Please contact us at Service@Desco.com for a quote.

2. Statfree i is available in fused sections. Please contact Service@Desco.com for sizes and pricing.

3. DPL Plus may be used in areas where carts or chairs pass through, but is not recommended where chairs or carts are in constant use.

© 2018 DESCO INDUSTRIES INC.
Employee Owned

Many Statfree® mats have lifetime electricals. See [technical drawing](#) and [limited warranty](#) for details.



Desco
Phone: West (909) 627-8178 | East (781) 821-8370
e-mail: Service@Desco.com
Web: Desco.com

