


Quad 4× RCA Phono Socket Right Angle PCB, Gold


pro-SIGNAL



Specifications

Max. Contact Resistance : 30mW
 Min. Insulation Resistance : 100mW, at 500V DC
 Dielectric Withstand Voltage : 500V AC for one minute

Diagram



Dimensions : Millimetres

Tolerance: ±0.2mm

No.	Part Name	Material	Remark	Qty
1	Contact Pin 1	H62M δ = 0.3	D.Cu/Sn	2
2	Contact Pin 2	H62M δ = 0.3	D.Cu/Sn	2
3	Outer Contact	H62M δ = 0.3	D.Au	4
4	Housing	ABS	White	1
5	Plastic ring	ABS	Black	2
6	Gasket	777D	-	4

Part Number Table

Description	Part Number
Quad 4× RCA Phono Socket Right Angle PCB, Gold	PSG01551

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
 Farnell.com/exclusive-brands
 Element14.com/exclusive-brands

pro-SIGNAL