



SAFETY DATA SHEET

according to Regulation (EU) 2015/830

Page 1/6

Reflect Wash & Wax

Revision 4

Revision date 2019-04-29

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name	Reflect Wash & Wax
--------------	--------------------

1.2. Relevant identified uses of the substance or mixture and uses advised against

Product Use	[SU22] Professional uses: Public domain (administration, education, entertainment, services, craftsmen); ----- [SU21] Consumer uses: Private households (= general public = consumers);
Description	Vehicle Shampoo. Wax.

1.3. Details of the supplier of the safety data sheet

Company	Future Developments Manufacturing Ltd
Address	Davenport Street Burslem Stoke on Trent ST6 4HS Staffordshire
Web	www.fdev.co.uk
Telephone	01782 826870
Email	sales@fdev.co.uk
Email address of the competent person	support@fdhost.co.uk

1.4. Emergency telephone number

Emergency telephone number	01782 829000 9.00am-5.00pm Mon - Fri
----------------------------	---

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

2.1.2. Classification - EC 1272/2008	Eye Irrit. 2: H319;
--------------------------------------	---------------------

2.2. Label elements

Hazard pictograms	
Signal Word	Warning
Hazard Statement	Eye Irrit. 2: H319 - Causes serious eye irritation.
Precautionary Statement: Prevention	P102 - Keep out of reach of children P264 - Wash thoroughly after handling. P280 - Wear protective gloves/protective clothing/eye protection/face protection.

Reflect Wash & Wax

Revision 4
Revision date 2019-04-29

2.2. Label elements

Precautionary Statement: Response	P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P337+P313 - If eye irritation persists: Get medical advice/attention.
--	--

2.3. Other hazards

Other hazards	SPILLAGE MAY CREATE SLIP HAZARD.
----------------------	----------------------------------

SECTION 3: Composition/information on ingredients

3.2. Mixtures

EC 1272/2008

Chemical Name	Index No.	CAS No.	EC No.	REACH Registration Number	Conc. (%w/w)	Classification
Sodium Lauroyl Sarcosinate		137-16-6	205-281-5		0.5 - 1%	Eye Dam. 1: H318;
Triethanolamine dodecylbenzene sulphonate		27323-41-7			0.5 - 1%	Skin Irrit. 2: H315; Eye Dam. 1: H318;
Coconut diethanolamide		68603-42-9			0.5 - 1%	Skin Irrit. 2: H315; Eye Dam. 1: H318;

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation	No precautions required to be mentioned.
Eye contact	Irritating to eyes. Rinse immediately with plenty of water for 15 minutes holding the eyelids open. Seek medical attention if irritation or symptoms persist.
Skin contact	May cause irritation to skin. Wash with water and soap as a precaution. Seek medical attention if irritation or symptoms persist.
Ingestion	Ingestion may cause nausea and vomiting. Seek medical attention if irritation or symptoms persist.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation	See section 4.1 for further information.
Eye contact	Irritating to eyes. Seek medical attention if irritation or symptoms persist.
Skin contact	Irritating to skin. Seek medical attention if irritation or symptoms persist.
Ingestion	Ingestion may cause nausea and vomiting. Seek medical attention if irritation or symptoms persist.

4.3. Indication of any immediate medical attention and special treatment needed

	No further relevant information available.
--	--

SECTION 5: Firefighting measures

5.1. Extinguishing media

	Use extinguishing media appropriate to the surrounding fire conditions.
--	---

5.2. Special hazards arising from the substance or mixture

	Burning produces irritating, toxic and obnoxious fumes.
--	---

5.3. Advice for firefighters

	Wear suitable respiratory equipment when necessary.
--	---

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

	No precautions required to be mentioned.
--	--

6.2. Environmental precautions

	Do not allow product to enter drains. Prevent further spillage if safe.
--	---

6.3. Methods and material for containment and cleaning up

Reflect Wash & Wax

Revision 4

Revision date 2019-04-29

6.3. Methods and material for containment and cleaning up

Absorb with inert, absorbent material. Sweep up. Transfer to suitable, labelled containers for disposal. Clean spillage area thoroughly with plenty of water.

6.4. Reference to other sections

See section 2,3,8,13 for further information.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Avoid contact with eyes and skin. Adopt best Manual Handling considerations when handling, carrying and dispensing.

7.2. Conditions for safe storage, including any incompatibilities

Keep in a cool, dry, well ventilated area. Keep containers tightly closed. Store in correctly labelled containers.

7.3. Specific end use(s)

See section 1.2 for further information.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

See section 8.2 for further information.

8.2. Exposure controls



8.2.1. Appropriate engineering controls

SPILLAGE MAY CREATE SLIP HAZARD.

8.2.2. Individual protection measures

Wear suitable protective clothing.

Eye / face protection

Approved safety goggles.

Skin protection -

Chemical resistant gloves (PVC).

Handprotection

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Reflect Wash & Wax

Revision 4

Revision date 2019-04-29

9.1. Information on basic physical and chemical properties

Appearance	Liquid
Colour	Various
Odour	Characteristic
Odour threshold	No data available
Freezing Point	No data available
Initial boiling point	No data available
Evaporation rate	No data available
Flammability (solid, gas)	No data available
Vapour pressure	No data available
Vapour density	No data available
Relative density	No data available
Fat Solubility	No data available
Partition coefficient	No data available
Autoignition temperature	No data available
Viscosity	No data available
Explosive properties	No data available
Oxidising properties	No data available
Melting point	No data available
Flash point	No data available
Solubility	Soluble in water

9.2. Other information

Conductivity	No data available
Surface tension	No data available
Gas group	No data available

SECTION 10: Stability and reactivity

10.1. Reactivity

	Stable under normal conditions.
--	---------------------------------

10.2. Chemical stability

	Stable under normal conditions.
--	---------------------------------

10.3. Possibility of hazardous reactions

	No data is available on this product.
--	---------------------------------------

10.4. Conditions to avoid

	No data is available on this product.
--	---------------------------------------

10.5. Incompatible materials

	No data available.
--	--------------------

10.6. Hazardous decomposition products

	No data is available on this product.
--	---------------------------------------

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity	Irritating to eyes and respiratory system.
Skin corrosion/irritation	Irritating to skin.
Serious eye damage/irritation	Irritating to eyes.
Germ cell mutagenicity	No data is available on this product.
Carcinogenicity	No data is available on this product.
Reproductive toxicity	No data is available on this product.

Reflect Wash & Wax

Revision 4

Revision date 2019-04-29

SECTION 12: Ecological information

12.1. Toxicity

No data available

12.2. Persistence and degradability

No data is available on this product.

12.3. Bioaccumulative potential

No data is available on this product.

Partition coefficient

Reflect Wash & Wax No data available

12.4. Mobility in soil

No data is available on this product.

12.5. Results of PBT and vPvB assessment

No data is available on this product.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Must be disposed of in accordance with local and national regulations.

General information

Dispose of in compliance with all local and national regulations.

SECTION 14: Transport information

14.1. UN number

The product is not classified as dangerous for carriage.

14.2. UN proper shipping name

The product is not classified as dangerous for carriage.

14.3. Transport hazard class(es)

The product is not classified as dangerous for carriage.

14.4. Packing group

The product is not classified as dangerous for carriage.

14.5. Environmental hazards

The product is not classified as dangerous for carriage.

14.6. Special precautions for user

The product is not classified as dangerous for carriage.

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

The product is not classified as dangerous for carriage.

Further information

The product is not classified as dangerous for carriage.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Reflect Wash & Wax

Revision 4

Revision date 2019-04-29

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

	The classification detailed on this safety data sheet refers to the neat material only. Dilution of the product may reduce the classification. This safety data sheet complies with the requirements of Regulation (EC) No. 1907/2006 & (EC) No. 1272/2008 & (EC) 1999/45.
--	--

15.2. Chemical safety assessment

	No information available.
--	---------------------------

SECTION 16: Other information

Other information

Text of Hazard Statements in Section 3	Eye Dam. 1: H318 - Causes serious eye damage. Skin Irrit. 2: H315 - Causes skin irritation.
---	--

Further information

	The information supplied in this Safety Data Sheet is designed only as guidance for the safe use, storage and handling of the product. This information is correct to the best of our knowledge and belief at the date of publication however no guarantee is made to its accuracy. This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any other process.
--	--