

Rolling TV/Monitor Cart - for Flat/Curved 32" to 70" TVs and Monitors

MODEL NUMBER: DMCS3270XP







Height-adjustable mobile TV stand hangs a flat- or curved-panel television or monitor and peripherals, such as a Blu-ray player, laptop and webcam.

Description

The DMCS3270XP Mobile TV Cart allows you to mount a flat- or curved-panel television, monitor or other display and move it from room to room for best viewing or against a wall out of the way when not in use. Recommended for classrooms, lecture halls, offices, auditoriums and conference rooms, the height-adjustable mobile stand fits most displays from 32 to 70 inches.

You can adjust this heavy-duty rolling TV stand's height from 47 to 81.5 inches. You can also rotate the display for viewing in portrait or landscape modes. Roll the unit with little effort to the proper viewing location and angle on sturdy four-inch swivel casters that move smoothly through doorways and over thresholds. All four casters lock to keep the stand securely in position.

A shelf mounted above the display holds projectors, webcams and laptops. A lower shelf holds other audio/video components, such as a Blu-ray player. Durable aluminum and steel construction supports up to 150 pounds. The adapter brackets can be adjusted to conform to VESA-compliant displays with any of the following mounting hole patterns: 200 x 200, 300 x 300, 400 x 200, 400 x 400 and 600 x 400.

Features

Height Adjustable Display Stand Rolls from Room to Room

- · Mobile mount for flat/curved-panel TVs, monitors and other displays
- · Recommended for classrooms, lecture halls, offices, auditoriums and conference rooms
- Fits most displays from 32 to 70 in.

Flexible Features That Meet Your Specifications

- Height adjusts from 47 to 81.5 in.
- · Rotates for viewing in portrait or landscape modes

Rolls on Sturdy Metal Casters

- 4 in. swivel casters move smoothly through doorways and over thresholds
- All casters lock to hold stand securely in position while at rest

Highlights

- Fits most flat or curved panel displays from 32 to 70 in.
- Designed for portrait or
 - landscape mounting
- Height adjusts from 47 to 81.5 in.
- Locking 4 in. swivel casters for easy movement
- Supports up to 150 lb.

Package Includes

- Middle base
- Left leg
- Right leg
- Left cover
- Right cover
- Support plate
- Universal plate
- (2) Plastic covers
- (2) Adapter brackets
- Column
- Plastic handle
- Top cover
- Connecting plate
- · Camera shelf
- DVD shelf
- (8) Washers
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M8 x 20 screws
- (4) M6 x 30 screws
- (4) M8 x 30 screws
- (4) M8 x 50 screws
- (8) M6 x 16 screws
- (3) M6 x 25 screws
- (7) M4 x 6 screws
- (2) M6 x 14 screws
- (6) M6 x 8 screws



Durable Construction

- Made from aluminum and steel
- Upper shelf holds projectors, webcams and laptops
- Lower shelf holds A/V components, such as Blu-ray player
- Supports up to 150 lb.

VESA Compliance

• Supports the following VESA mounting hole patterns: 200 x 200, 300 x 300, 400 x 200, 400 x 400 and 600 x 400

Specifications

OVERVIEW	
UPC Code	037332203328
PHYSICAL	
Mounting Location	Floor
Shipping Dimensions (hwd / in.)	44.72 x 20.87 x 9.65
Shipping Dimensions (hwd / cm)	113.59 x 53.01 x 24.51
Shipping Weight (lbs.)	59.00
Shipping Weight (kg)	26.76
Unit Dimensions (hwd / in.)	81.5 x 32.6 x 27.6
Unit Weight (lbs.)	46.2
Unit Weight (kg)	20.96
Material of Construction	Aluminum and steel
Color	Black; Silver
VESA Pattern (mm)	200x200; 300x300; 400x200; 400x400; 600x400
Motion	Full
Degrees of Motion	360° Rotate
Maximum Weight Capacity (lbs.)	150
Maximum Weight Capacity (kg)	68
Minimum Screen Size (in.)	32
Maximum Screen Size (in.)	70
Minimum Screen Size (cm)	81.28
Maximum Screen Size (cm)	177.8
Number of Displays	1

- (4) M8 x 25 screws
- (2) M5 x 8 screws
- (8) Small spacers
- (8) Big spacers
- Allen wrench
- Wrench
- Owner's manual



FEATURES & SPECIFICATIONS		
Tools Necessary	Yes	
Cord Management	No	
WARRANTY		
Product Warranty Period (Worldwide)	5-year limited warranty	

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies