

Touch panel - TP 3043W - 2402629

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Touch panel with 10,92 cm / 4,3"-TFT-display (analog resistive (polyester)), 480 x 272 pixel(s) (WQVGA), 262144 colors, Arm® Cortex®-A8, 800 MHz, 2x USB host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows® Embedded Compact 7 and user software: Visu+ / AX OPC Server. (bus system: without)

Similar figure



Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4055626244969
Weight per Piece (excluding packing)	600.000 g
Custom tariff number	84714100
Country of origin	Germany

Technical data

Dimensions

Outer dimensions: width, height, depth	140 mm x 100 mm x 5 mm (Dimensions of the front plate)
Installation dimensions: width, height, depth	132 mm x 92 mm x 42 mm (Installation cutout)

Display

Display	10,92 cm / 4,3"-TFT
Screen resolution	480 x 272 Pixel(s) (WQVGA)
Touch technology	analog resistive (polyester)
Brightness	385 cd/m ² typical (adjustable)
Backlighting	LED
Display backlight MTBF	40000 h
Colors	262144 colors
Reading angle left	69 °
Reading angle right	69 °
Reading angle top	75 °

Touch panel - TP 3043W - 2402629

Technical data

Display

Reading angle bottom	75 °
----------------------	------

Computer data

Processor	Arm® Cortex®-A8, 800 MHz
Operating system	Windows® Embedded Compact 7
User software	Visu+
	AX OPC Server
RAM	512 MB RAM
Mass storage	Flash, 1 GB
Network	1 x Ethernet (10/100 Mbps), RJ45
Interfaces	2x USB host 2.0
Bus system	without
Slots	1x SD
Realtime clock	Yes (battery-backed)
Service life of battery	5 years (typical)

General

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated
Mounting type	Front installation
Weight	600 g

Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
	NEMA 4X
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	20 % ... 85 % (non-condensing)
Permissible humidity (storage/transport)	20 % ... 85 % (non-condensing)
Vibration (operation)	DIN EN 60068-2-6
Shock	DIN EN 60068-2-27

Device supply

Supply voltage	24 V DC
Supply voltage range	18 V DC ... 30 V DC
Typical current consumption	0.2 A
Power consumption	typ. 4.8 W
Power supply unit	24 V DC ±20 %

Standards and Regulations

Shock	DIN EN 60068-2-27
Vibration (operation)	DIN EN 60068-2-6

Environmental Product Compliance

Touch panel - TP 3043W - 2402629

Technical data

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 15;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	27330200
eCl@ss 4.1	27330200
eCl@ss 5.0	27330200
eCl@ss 5.1	27330200
eCl@ss 6.0	27242300
eCl@ss 7.0	27242302
eCl@ss 8.0	27242302
eCl@ss 9.0	27330201

ETIM

ETIM 2.0	EC001426
ETIM 3.0	EC001426
ETIM 4.0	EC001412
ETIM 5.0	EC001412
ETIM 6.0	EC001412
ETIM 7.0	EC001412

UNSPSC

UNSPSC 6.01	43172403
UNSPSC 7.0901	43211903
UNSPSC 11	43172403
UNSPSC 12.01	43211903
UNSPSC 13.2	43211904
UNSPSC 18.0	43211904
UNSPSC 19.0	43211904
UNSPSC 20.0	43211904
UNSPSC 21.0	43211904

Approvals

Approvals

Approvals

UL Listed / cUL Listed / cULus Listed

Touch panel - TP 3043W - 2402629

Approvals

Ex Approvals

UL Listed / cUL Listed / cULus Listed

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 205795
-----------	--	---	---------------

cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 205795
------------	--	---	---------------

cULus Listed			
--------------	--	--	--

Accessories

Accessories

Battery module

Battery / accumulator - HMI BATTERY - 2701383

Lithium battery



Mounting material

Mounting material - HMI SCB MOUNTING KIT 4 - 2701384



HMI mounting kit for installation on a front plate. The mounting kit includes 4 x mounting brackets, 4 x screw threads, and a hexagonal wrench.

Touch panel - TP 3043W - 2402629

Accessories

Mounting material - HMI WALL MOUNTING KIT - 2701380

HMI mounting kit for panel installation. The mounting kit includes 2 spring clips.



Operating stylus

Touch pen - TOUCH PEN - 2701379



Touch pen for analog-resistive HMIs, silver coated. Delivery includes self-adhesive pen holder.

Parameterization memory

Program / configuration memory - SD FLASH 2GB - 2988162



Program and configuration memory, for extending the internal flash memory, pluggable, 2 GB.

PCB plug

Printed-circuit board connector - MC 1,5/ 3-STF-3,5 BD:1-3 - 1751312



PCB connector, nominal current: 8 A, rated voltage (III/2): 160 V, Nominal cross section: 1.5 mm², number of positions: 3, pitch: 3.5 mm, connection method: Screw connection with tension sleeve, color: green, contact surface: Tin

Storage medium

USB memory stick - USB FLASH DRIVE - 2402809



USB memory stick, 8 GB

