## PHYSICAL INFRASTRUCTURE SYSTEMS

B. Copper Systems

C. Fiber **Optic** Systems

D. Power over Ethernet

E. Zone Cabling

Wireless

**Outlets** 

Н. Media Distribution

Ι. **Physical** Infrastructure Management

J. Overhead & Underfloor Routing

Surface Raceway

L. Cabinets, Racks & Cable Management

M. **Grounding & Bonding** 

Industrial

0. Labeling & Identification

Cable Management Accessories

> 0. Index

## IndustrialNet<sup>™</sup> TX5e<sup>™</sup> Patch Cords

- Exceed ANSI/TIA-568-C.2 Category 5e and ISO 11801 Class D standards
- Meet requirements of IEEE 802.3af and IEEE 802.3at for PoE applications
- Each patch cord is 100% performance tested and wired to T568B
- Constructed of industrial Category 5e, 24 AWG UTP or 26 AWG shielded stranded cable and modular plugs for superior performance
- Plug contacts plated with 50 microinches of gold for superior performance
- Plug meets all applicable ANSI/TIA/EIA-968-A requirements and exceeds IEC 60603-7 specifications
- Bulkhead provides IP67/IP65 seal when mated to an IP67/IP65, NEMA 6 or 6P bulkhead connector
- Patch cords are pre-terminated and provide IP67/IP65 seal when mated to IP67/IP65 bulkhead connectors
- Available with or without dust caps





		Length		Std. Pkg.			
Part Number	Part Description	Ft.	m	Qty.	Qty.		
IndustrialNet™ TX5e™ UTP Patch Cords							
IUTPCH3BLY*	Patch cord constructed of industrial grade UTP Category 5e stranded cable with modular plugs. Includes dust caps.	3	0.91	1	10		
IUTPCHNC3BLY*	Patch cord constructed of industrial grade UTP Category 5e stranded cable with modular plugs. Does not include dust caps.	3	0.91	1	10		
IndustrialNet™ TX5e™ Shielded Patch Cords							
ISTPCH1MBLY**	Patch cord constructed of industrial grade shielded Category 5e stranded cable with shielded modular plugs. Includes dust caps.	3.28	1	1	10		
ISTPCHNC1MBLY**	Patch cord constructed of industrial grade shielded Category 5e stranded cable with shielded modular plugs. Does not include dust caps.	3.28	1	1	10		

<sup>\*</sup>For lengths other than 3 feet (5, 7, 10, 15, or 20 feet) change the length designation in the part number to the

## IndustrialNet™ LC Fiber Optic Bulkhead Adapter and Patch Cords

- IndustrialNet<sup>™</sup> Patch Cords are pre-terminated and provide IP67 seal when mated to IP67 bulkhead adapters
- Patch cords built with 62.5µm multimode duplex industrial-grade jacketed fiber cable
- · Ideal for daisy-chaining hardened industrial switches between IP66 rated enclosures
- · Pigtails are ideal for routing fiber through conduit
- Patch cords are 100% factory tested for insertion loss
- Insertion loss data is recorded for every multimode patch cord, providing lifetime traceability to a QC number, labeled on each patch cord



Part Number	Part Description	Std. Pkg. Qty.	Ctn.		
IndustrialNet™ LC Fiber Optic Bulkhead Adapter					
IAEF7JMA‡	Industrial LC fiber bulkhead adapter.	1	10		
IndustrialNet™ LC Fiber Optic Patch Cord and Pigtail					
IAEF617P-7PM1*	Industrial duplex multimode 62.5µm LC to LC patch cord.	1	10		
IAEF617P-NM1**	Industrial duplex multimode 62.5µm LC to pigtail.	1	10		

‡Bulkhead includes duplex multimode LC adapter with phosphor bronze split sleeves.

\*For lengths other than one meter (2, 3, 10, 20, and 30 meter lengths) change the length description in the part number to the desired lengths.

\*\*Contact Panduit Customer Service for pigtail lengths and/or discrete length patch cords with LC fiber interface.

<sup>\*\*</sup>For lengths other than 1 meter (2, 3, or 5 meters) change the length designation in the part number to the