

# Touch panel - TP 3154W - 2402631

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Touch panel with 39.12 cm / 15.4"-TFT-display (analog resistive (polyester)), 1280 x 800 pixel(s) (WXGA), 65536 colors, Arm® Cortex®-A8, 800 MHz, 2x USB host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows® Embedded Compact 7 and user software: Visu+ / AX OPC Server. (bus system: without)

Similar figure



## Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4055626246406
Weight per Piece (excluding packing)	1,900.000 g
Custom tariff number	84714100
Country of origin	Germany
Note	Made to Order (non-returnable)

## Technical data

### Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

### Dimensions

Outer dimensions: width, height, depth	420 mm x 297 mm x 5 mm (Dimensions of the front plate)
Installation dimensions: width, height, depth	396 mm x 273 mm x 64 mm (Installation cutout)

### Display

Display	39.12 cm / 15.4"-TFT
Screen resolution	1280 x 800 Pixel(s) (WXGA)
Touch technology	analog resistive (polyester)
Brightness	360 cd/m <sup>2</sup> typical (adjustable)
Backlighting	LED
Display backlight MTBF	50000 h

# Touch panel - TP 3154W - 2402631

## Technical data

### Display

Colors	65536 colors
Reading angle left	80 °
Reading angle right	80 °
Reading angle top	70 °
Reading angle bottom	70 °

### Computer data

Processor	Arm® Cortex®-A8, 800 MHz
Operating system	Windows® Embedded Compact 7
User software	Visu+
	AX OPC Server
RAM	512 MB RAM
Mass storage	Flash, 1 GB
Network	1 x Ethernet (10/100 Mbps), RJ45
Interfaces	2x USB host 2.0
Bus system	without
Slots	1x SD
Realtime clock	Yes (battery-backed)
Service life of battery	5 years (typical)

### General

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated
Mounting type	Front installation
Weight	1900 g

### Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
	NEMA 4X
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	20 % ... 85 %
Vibration (operation)	1g, according to EN 60068-2-6
Shock	15g, according to IEC 60068-2-27

### Device supply

Supply voltage	24 V DC
Supply voltage range	18 V DC ... 30 V DC
Typical current consumption	0.9 A
Power consumption	typ. 21.6 W
Power supply unit	24 V DC ±20 %

### Standards and Regulations

# Touch panel - TP 3154W - 2402631

## Technical data

### Standards and Regulations

Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 15;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Classifications

### eCl@ss

eCl@ss 4.0	27330200
eCl@ss 4.1	27330200
eCl@ss 5.0	27330200
eCl@ss 5.1	27330200
eCl@ss 6.0	27242300
eCl@ss 7.0	27242302
eCl@ss 8.0	27242302
eCl@ss 9.0	27330201

### ETIM

ETIM 2.0	EC001426
ETIM 3.0	EC001426
ETIM 4.0	EC001412
ETIM 5.0	EC001412
ETIM 6.0	EC001412
ETIM 7.0	EC001412

### UNSPSC

UNSPSC 6.01	43172403
UNSPSC 7.0901	43211903
UNSPSC 11	43172403
UNSPSC 12.01	43211903
UNSPSC 13.2	43211904
UNSPSC 18.0	43211904
UNSPSC 19.0	43211904
UNSPSC 20.0	43211904
UNSPSC 21.0	43211904

## Approvals

### Approvals

# Touch panel - TP 3154W - 2402631

## Approvals

---

### Approvals

UL Listed / cUL Listed / cULus Listed

---

### Ex Approvals

UL Listed / cUL Listed / cULus Listed

---

## Approval details

UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 205795
cUL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 205795
cULus Listed			

## Accessories

### Accessories

#### Battery module

Battery / accumulator - HMI BATTERY - 2701383

Lithium battery



#### Mounting material

Mounting material - HMI SCB MOUNTING KIT 8 - 2701387



HMI mounting kit for installation on a front plate. The mounting kit includes 8 x mounting brackets, 8 x screw threads, and a hexagonal wrench.

---

# Touch panel - TP 3154W - 2402631

## Accessories

Mounting material - HMI WALL MOUNTING KIT - 2701380

HMI mounting kit for panel installation. The mounting kit includes 2 spring clips.



---

## Operating stylus

Touch pen - TOUCH PEN - 2701379



Touch pen for analog-resistive HMIs, silver coated. Delivery includes self-adhesive pen holder.

---

## Parameterization memory

Program / configuration memory - SD FLASH 2GB - 2988162



Program and configuration memory, for extending the internal flash memory, pluggable, 2 GB.

---

## PCB plug

Printed-circuit board connector - MC 1,5/ 3-STF-3,5 BD:1-3 - 1751312



PCB connector, nominal current: 8 A, rated voltage (III/2): 160 V, Nominal cross section: 1.5 mm<sup>2</sup>, number of positions: 3, pitch: 3.5 mm, connection method: Screw connection with tension sleeve, color: green, contact surface: Tin

---

## Storage medium

USB memory stick - USB FLASH DRIVE - 2402809



USB memory stick, 8 GB

