

MAX540H190S

- Waterproof and dustproof IP67 certified
- Mil Specs (STANAG 4280, DEF STAN 81-41)
- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Holes for double padlocking
- Stackable interlocking system
- Thick body material
- Fully length hinges
- Nylon pins, corrosion free

Body and handle: polypropylene copolymer

Latches: nylon

Pins: nylon + 30% fiberglass

O-ring: polymer

COLOURS: Black

EXTERNAL DIMENSIONS: 594 x 473 x H215 mm (23.39 x 18.62 x H8.46 inch)

INTERNAL DIMENSIONS: 538 x 405 x H190 mm (21.18 x 15.94 x H7.48 inch)

LID-BOTTOM DEPTH: 50 + 140 mm (1.97 + 5.51 inch)

WEIGHT WITH FOAM: 5,40 Kg

CARTON DIMENSIONS: 620 x 500 x 240mm (24.40 x 19.68 x 9.45 inch)

PCS PER CARTON: 1

WEIGHT OF THE FULL CARTON WITH FOAMS: 6.47 Kg - 14.26 Lbs

MOULDING: injection molded

RANGE TEMPERATURE: -30 / 90°C (-22 / 194°F)

FEATURES: IP67, STANAG 4280, DEF STAN 81-41

CUSTOMIZATION: personalized nameplate/ resin label

ACCESSORIES: cubed foams, lid organizer

