

# Han Guiding Relay module, female



Part number	09 14 003 3151
Specification	Han Guiding Relay module, female
HARTING eCatalogue	https://b2b.harting.com/09140033151
Features	2 contacts with relay function (last mate - first break)

#### Identification

Category	Modules
Series	Han-Modular <sup>®</sup>
Type of module	Han <sup>®</sup> Guiding module
Description of the module	Relay module

#### Version

Termination method	Crimp termination
Gender	Female
Number of contacts	3
Details	Please order crimp contacts separately.

## **Technical characteristics**

Conductor cross-section	0.14 4 mm²
Rated current	16 A
Rated voltage	500 V
Rated impulse voltage	6 kV
Pollution degree	3
Insulation resistance	>10 <sup>10</sup> Ω
Limiting temperature	-40 +125 °C
Mating cycles	≥500
Lock-in range	±4 mm

## Material properties

	Material (insert)	Polycarbonate
--	-------------------	---------------

Page 1 / 2 | Creation date 2019-07-09 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



### Material properties

Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
Specifications and approvals	
Specifications	EN 60664-1 IEC 61984
Commercial data	
Packaging size	2
Net weight	9.2 g
Country of origin	China
European customs tariff number	8547200000