

CM-MPS.21P



CM-MPS.21P Three-phase monitoring relay 2c/o, 0,0.1-30s, L1-L2-L3-N=3x180-280VAC

General Information

Extended Product Type	CM-MPS.21P
Product ID	1SVR740885R3300
EAN	4016779852074
Catalog Description	CM-MPS.21P Three-phase monitoring relay 2c/o, 0,0.1-30s, L1-L2-L3-N=3x180-280VAC
Long Description	<p>The CM-MPS.21P is a multifunctional relay from the CM three-phase monitors range. It operates with a rated control supply voltage / three-phase measuring voltage of 180-280 V AC 50/60 Hz and has a 2 c/o (SPDT) output with contacts rated at 250 V / 4 A. This relay is also suitable to monitor single-phase mains. It monitors all phase parameters such as over/undervoltage, phase unbalance, phase failure as well as an interrupted neutral. The corresponding threshold values are adjustable. Phase sequence monitoring as well as an ON or OFF tripping delay are selectable. The tripping delay is adjustable over a range of instantaneous to 30 s (0, 0.1-30 s). A sealable transparent cover for protection against unauthorized changes is available as accessory. The device offers maintenance free Easy Connect Technology with push-in terminals.</p>

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

Popular Downloads

Data Sheet, Technical Information	2CDC112206D0201
Instructions and Manuals	1SVC730520M0000

Dimensions

Product Net Width	22.5 mm
Product Net Depth / Length	103.7 mm
Product Net Height	85.6 mm
Product Net Weight	0.135 kg

Technical

Function	Phase failure detection Phase sequence monitoring Over- and undervoltage monitoring Phase unbalance detection Interrupted neutral monitoring
Standards	CAN/CSA C22.2 No.14 EN 50581

IEC/EN 60255-27
 IEC/EN 61000-6-2
 IEC/EN 61000-6-3
 UL 508

Measuring Range	(L-N) 180 ... 280 V AC
Rated Control Supply Voltage (U_s)	(L-N) 180 ... 280 V AC
Rated Frequency (f)	Supply Circuit 50/60 Hz
Output	2 c/o (SPDT) contacts
Time Range	200 ms start-up delay 0 s or 0.1 ... 30 s tripping delay (ON or OFF)
Terminal Type	Screwless Terminals
Rated Operational Current AC-12 (I_{θ})	(230 V) 4 A
Rated Operational Current AC-15 (I_{θ})	(230 V) 3 A
Rated Operational Current DC-12 (I_{θ})	(24 V) 4 A
Rated Operational Current DC-13 (I_{θ})	(24 V) 2 A
Minimum Switching Capacity	24 V 10 mA
Rated Insulation Voltage (U_i)	Input Circuit / Output Circuit 600 V Output Circuit 1 / Output Circuit 2 300 V
Rated Impulse Withstand Voltage (U_{imp})	Input Circuit 6 kV Output Circuit 4 kV
Degree of Protection	Housing IP50 Terminals IP20
Overvoltage Category	III
Pollution Degree	3
Short-Circuit Protective Devices	Output Circuit NC - F Type Fuses 6 A Output Circuit NO - F Type Fuses 10 A
Electrical Durability	AC-12 100000 cycle
Mechanical Durability	30000000 cycle
Connecting Capacity	Flexible with Ferrule 2x 0.5 ... 1.5 mm ² Flexible with Insulated Ferrule 2x 0.5 ... 1.5 mm ² Flexible 2x 0.5 ... 1.5 mm ² Rigid 2x 0.5 ... 1.5 mm ²
Wire Stripping Length	8 mm
Mounting Position	Any
Mounting on DIN Rail	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715

—

Environmental

Ambient Air Temperature	Operation -25 ... +60 °C Storage -40 ... +85 °C
RoHS Status	Following EU Directive 2011/65/EU

—

Technical UL/CSA

Maximum Operating Voltage UL/CSA	Output Circuit 300 V AC
Contact Rating UL/CSA	B300
Connecting Capacity UL/CSA	Flexible 2x 18-16 AWG Rigid 2x 20-16 AWG

—

Certificates and Declarations (Document Number)

CB Certificate	CB_DK-27947-UL
CCC Certificate	CCC_2009010303326655
cULus Certificate	cULus508_20120829-E140448
Declaration of Conformity - CE	1SVD981014-0002
DNV GL Certificate	DNV_GL_TAA000017D
EAC Certificate	EAC_RU_C-DE.ME77.B.03424
Environmental Information	1SAA981020-2401
Instructions and Manuals	1SVC730520M0000
RMRS Certificate	RMRS_1740020250
RoHS Information	1SVD981014-0002

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	97 mm
Package Level 1 Height	109 mm
Package Level 1 Depth / Length	30 mm
Package Level 1 Gross Weight	0.16 kg
Package Level 1 EAN	4016779852074

Classifications

Object Classification Code	B
ETIM 4	EC001441 - Phase monitoring relay
ETIM 5	EC001441 - Phase monitoring relay
ETIM 6	EC001441 - Phase monitoring relay
ETIM 7	EC001441 - Phase monitoring relay
eClass	7.0 27371803
UNSPSC	39121536
E-Number (Sweden)	3860609

Categories

Low Voltage Products and Systems → Control Products → Electronic Relays and Controls → Three Phase Monitors

