

Compact 5-in-1 CCTV Tester



- 8MP TVI / 4MP CVI / 5MP AHD / 4K IP / CVBS
- H.265 / H.264, 4K video display
- Dahua, HikVision and Axis ONVIF camera test
- Rapid ONVIF, auto view video and create testing report
- DC12V 3A, DC48V PoE power output
- Built in WIFI,
- Innovative coaxial HD focus and video signal quality test
- 10 / 100 / 1000Mbps Ethernet, network state and traffic display
- TesterPlay: Android version mobile phone and PC display at the same time



Applications


Designed for testing installations of IP, analogue and HD coaxial cameras as well as other security equipment. This IP camera tester features a 4 inch 800 x 480 pixel high resolution touch screen. The tester supports several ONVIF PTZ and analogue PTZ controls.

No need carry a variety of testers, this compact all-in-one unit is designed to make your life simpler.

- CCTV system installation
- Network cabling projects
- 4K H.265 IP camera testing
- Video transmission channel testing
- PTZ controller

Camera tests:

- AXIS, Hikvision camera test, enter ONVIF app, input username and password to test
- CVBS camera test and PTZ control
- IPC TEST (Non - ONVIF test), HIK test tool (Hikvision camera), DH test tool (Dahua camera)
- IP discovery, one key to detect all network cameras IP addresses
- Rapid video, one key to detect all network cameras and auto display
- DC12V 3A power output / PoE DC48V power output, Max power 24W
- Built in Wi-Fi, display image from the wireless camera, creates a Wi-Fi hotspot



Kit Contents

- 1x CCTV tester unit
- 1x Hard protective carry case
- 1x 12V=1A Plug-in charger/PSU
- 1x 3.5mm Jack to crocodile clips test lead
- 1x RS485 to crocodile clips test lead
- 1x Jack power test lead
- 1x BNC test lead

Specifications			
LCD	Display	4 inch IPS touch screen, 800 x 480 pixel resolution	
Video	CVBS	1 channel BNC input, auto adapt NTSC/PAL PTZ and RS485 control, Baud 600-11520bps multiple protocols	
	IP test 4K	IP discovery/Quick ONVIF/IPC test/RTSP play/Client APK	
		Rapid Video	Auto view and create report
		HIK test tool	One key activation, image test and modify parameters
	Dahua test tool	Camera test and modify parameters	
	Coaxial HD	8MP TVI / 4MP CVI / 5MP AHD	
	Image	Zoom, screen snapshot, save, view, record and playback	
	Power	DC12V-3A to power camera while testing	
PoE Power		48V PoE Max. 24W	
Network test		Link monitor, port flashing, ping test	
Audio test		1 channel audio signal input	
Data Monitor		Capture and analyse command data from control device	