

SYLVANIA Luminaires

Slim Floodlight



Product Features

- Lightweight, compact design
- IP66 Rated with wide flood distribution
- High Efficacy meeting DLC Premium requirements*
- Applications: landscape, flood and signage applications

Wattage Comparison Chart


Slim Floodlight

Traditional Source	Traditional System Wattage	LED System Wattage	Energy Savings
35 W HPS	42	20	52%
50 W HPS	62	20	68%
70 W MH	91	20	78%
150 Q Halogen	150	20	87%
50 W HPS	62	30	52%
70 W HPS	91	30	67%
100 W HPS	120	30	67%
100 W MH	130	30	69%
200 W Q Hal	200	30	85%
150 W HPS	170	50	71%
150 W MH	188	50	73%
175 W MH	210	50	76%
175 W MH	210	100	52%
250 W MH	290	100	66%
250 W HPS	295	100	66%


Catalog #	Type
Project	
Notes	
Date	
Prepared by	

Dimensions

20-50W



100W



	20-30W	50W	100W
Width (W)	9.1in (230mm)	10.6in (270mm)	10.6in (270mm)
Height (H)	7.7in (195mm)	8.5in (217mm)	8.5in (217mm)
Total Height (TH)	10.5in (266mm)	11.3in (286mm)	11.3in (286mm)

Specifications

Weight: 20W/30W: 3.5lbs (1.6kg) 50W: 5lbs (2.3kg) 100W: 8lbs (3.6kg)

Construction: Two-piece cast aluminum with powder coat paint finish and glass lens. The standard color is bronze.

LED System: LED system with a life rating of $\geq 150,000$ hours at L_{70} @25°C. Luminaire efficacy up to 121 LPW.

Electrical: Offered in 20, 30, 50 and 100 Watts, the luminaire is designed to operate through the 120-277 VAC voltage. The LED driver has a 4kV surge suppression and is a constant current device, meeting UL1310 and UL48 Class 1 with built-in over temperature protection. The power factor is $\geq 90\%$ and THD is $\leq 20\%$.

Color Characteristics: CRI > 80 ; CCT of 3000K, 4000K or 5000K

Optics: Wide distribution with clear glass lens.

Installation: Luminaire includes 1/2" NPS for mounting to junction box for 20-50W, trunnion mount for 100W.

Operating Temperature: -40°F to +104°F (-40°C to +40°C).

Listings: cULus listed to UL1598 standards for wet locations and IP66 rated.

Warranty: Standard 5-year luminaire warranty (LEDLUM001).

Note: Specifications subject to change without notice. IES files available online.



*See page 2 for DLC listings.

Ordering Guide

Item Number:

SLMFLD	1A	/	XXX	UNV	8	XX	/	WF	/	BZ
Product Name	Generation		Wattage	Voltage	CRI	Color Temp (CCT)		Optics		Color/Finish
SLMFLD	1A		020 = 20W 030 = 30W 050 = 50W 100 = 100W	UNV = 120-277V	8 = > 80	30 = 3000K* 40 = 4000K 50 = 5000K		WF = Wide Flood		BZ = Bronze

*3000K only available in 20W version.

LEDLUM018R3 3-18




Photometric Data

20/30W*

SLMFLD1A/0X0UNV8X0/WF/BX


Isofootcandle Lines at 10' Mounting Height



50W

SLMFLD1A/050UNV840/WF/BZ


Isofootcandle Lines at 10' Mounting Height



100W

SLMFLD1A/100UNV8X0/WF/BZ

Isofootcandle Lines at 10' Mounting Height



For other mounting heights apply the following multipliers:

Mounting Height	6'	8'	10'	12'	15'
Multiplier	2.8	1.6	1.00	0.69	0.44

*For 30W please use 1.5 multiplier+

Ordering Information

Item Number	Ordering Abbreviation	Power (W)	Input Voltage	CRI	Color Temp (CCT)	Distribution	Total Fixture Lumens	LPW*	DLC**
74906	SLMFLD1A/020UNV830/WF/BZ	20	120-277V	>80	3000K	Wide Flood	2000	103	Std
74907	SLMFLD1A/020UNV840/WF/BZ	20	120-277V	>80	4000K	Wide Flood	2200	111	Prm
74908	SLMFLD1A/030UNV840/WF/BZ	30	120-277V	>80	4000K	Wide Flood	3400	110	Prm
74909	SLMFLD1A/030UNV850/WF/BZ	30	120-277V	>80	5000K	Wide Flood	3500	114	Prm
74910	SLMFLD1A/050UNV840/WF/BZ	50	120-277V	>80	4000K	Wide Flood	6100	119	Prm
74911	SLMFLD1A/050UNV850/WF/BZ	50	120-277V	>80	5000K	Wide Flood	6300	121	Prm
60108	SLMFLD1A/100UNV840/WF/BZ	100	120-277V	>80	4000K	Wide Flood	12,300	123	-
60109	SLMFLD1A/100UNV850/WF/BZ	100	120-277V	>80	5000K	Wide Flood	12,300	123	-

*LPW per LM79 report

**Prm is for DLC Premium, Std is for DLC Standard

For further information and to learn more about utility rebates, contact your local SYLVANIA sales representative.

LEDVANCE LLC

200 Ballardvale Street

Wilmington, MA 01887 USA

Phone 1-800-LIGHTBULB (1-800-544-4828)

www.sylvania.com

SYLVANIA and LEDVANCE are registered trademarks.

All other trademarks are those of their respective owners.

Licensee of product trademark SYLVANIA in general lighting.

Specifications subject to change without notice.

