
Piezo Buzzer

multicomp PRO

RoHS Compliant





Ø23

Specifications

Operating Voltage

Max. Rated Current

Resonant Frequency

Operating Temperature

Store Temperature

Rated Voltage

Tone Nature

Weight

Case Material

Dimensions : Millimetres

Part Number Table

: 12V DC

Min. Sound Pressure Level : 95dB at 12V DC / 10cm

: 8V DC to 24V DC

: 15mA at 12V DC

: 2.9 +0.5kHz

: Continuous

: -20 to +80°C

: -30 to +100°C

: PC

: 5g

Description	Part Number
Piezo Buzzer, 15mA, 95dB	MCKPI-G2329-3670

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farmell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

