

**RoHS  
Compliant**




## Features

- High power, high saturation inductors.
- MCPS1608 can help to achieve longer battery life significantly in handheld communication devices.
- MCPS3316 / 5022 designed for the higher current requirements of portable computers.
- MCPS1608 used ceramic base with gold-plating.
- MCPS3316 / 5022 used LCP plastic base. The others used LCP plastic base.

## Applications

- Portable telephones.
- Personal computers.
- DC/DC converters, etc.
- Other various electronic appliances.

## Diagram



## Dimensions

Type	A Maximum	B Maximum	C Maximum	D	E	F	H	I	J
MCPD1608	6.6	4.45	2.92	4.32	1.27	1.02	3.56	1.4	4.06
MCPD3316	12.95	9.4	5.21	7.62	2.54	2.54	2.79	2.92	7.37
MCPD5022	18.54	15.24	7.11	12.7	2.54	2.54	2.79	2.92	12.45

Dimensions : Millimetres

## Inductance and Rated Current Ranges


MCPD1608	1 $\mu$ H to 1000 $\mu$ H	9A to 0.3A
MCPD3316	0.47 $\mu$ H to 1000 $\mu$ H	40A to 0.8A
MCPD5022	1 $\mu$ H to 1000 $\mu$ H	20A to 1A

Electrical Specifications at 25°C

## Characteristics

Saturation Rated Current : The current when the inductance becomes 10% lower than its initial value. (Ta = 25°C).  
 Operating Temperature Range : -40°C to 85°C

## Part Number Identification



## Electrical Characteristics

### MCPD1608 Type

Codes	L (µH)	Tolerance	Test Condition		DCR (Ω) Maximum	SRF Reference (MHz)	Q Minimum	I rms (A) Maximum
			L	Q				
1R0	1	M	100kHz, 0.1V	200kHz, 0.1V	0.04	250	30	3
1R5	1.5	M	100kHz, 0.1V	200kHz, 0.1V	0.045	125	30	2.3
2R2	2.2	M	100kHz, 0.1V	200kHz, 0.1V	0.05	120	40	1.8
3R3	3.3	M	100kHz, 0.1V	200kHz, 0.1V	0.055	120	40	1.6
4R7	4.7	M	100kHz, 0.1V	200kHz, 0.1V	0.06	105	40	1.4
6R8	6.8	M	100kHz, 0.1V	200kHz, 0.1V	0.065	50	40	1.2
100	10	M	100kHz, 0.1V	200kHz, 0.1V	0.075	38	40	1
150	15	M	100kHz, 0.1V	100kHz, 0.1V	0.09	33	40	0.8
220	22	M	100kHz, 0.1V	100kHz, 0.1V	0.11	25	40	0.7
330	33	M	100kHz, 0.1V	100kHz, 0.1V	0.19	20	40	0.6
470	47	M	100kHz, 0.1V	100kHz, 0.1V	0.23	20	40	0.5
680	68	M	100kHz, 0.1V	100kHz, 0.1V	0.29	15	40	0.4
101	100	M	100kHz, 0.1V	100kHz, 0.1V	0.48	10	40	0.3
151	150	M	100kHz, 0.1V	100kHz, 0.1V	0.59	9	40	0.26
221	220	M	100kHz, 0.1V	100kHz, 0.1V	0.9	6	40	0.22
331	330	M	100kHz, 0.1V	100kHz, 0.1V	1.4	5	40	0.2
471	470	M	100kHz, 0.1V	100kHz, 0.1V	1.8	4	40	0.19
681	680	M	100kHz, 0.1V	100kHz, 0.1V	2.2	3	40	0.18
102	1000	M	100kHz, 0.1V	100kHz, 0.1V	3.4	2	40	0.15

Codes	L (μH)	Tolerance	Test Condition		DCR (Ω) Maximum	SRF Reference (MHz)	Q Minimum	I rms (A) Maximum
			L	Q				
152	1500	M	100kHz, 0.1V	100kHz, 0.1V	4.2	2	50	0.12
222	2200	M	100kHz, 0.1V	100kHz, 0.1V	8.5	2	50	0.10
332	3300	M	100kHz, 0.1V	100kHz, 0.1V	11	1	50	0.08
472	4700	M	100kHz, 0.1V	100kHz, 0.1V	13.9	1	50	0.06
682	6800	M	100kHz, 0.1V	100kHz, 0.1V	25	1	50	0.04
103	10000	M	100kHz, 0.1V	100kHz, 0.1V	32.8	0.8	50	0.02

### MCPS3316 Type

Codes	L (μH)	Tolerance	Test Condition	DCR (Ω) Maximum	SRF Reference (MHz)	IDC (A) Maximum	I rms (A) Maximum
1R0	1	M	100kHz, 0.1V	0.021	140	5.6	5
1R5	1.5	M	100kHz, 0.1V	0.022	120	5.2	4.5
2R2	2.2	M	100kHz, 0.1V	0.032	80	5	3.8
3R3	3.3	M	100kHz, 0.1V	0.039	70	3.9	3.3
4R7	4.7	M	100kHz, 0.1V	0.054	40	3.2	2.7
6R8	6.8	M	100kHz, 0.1V	0.075	38	2.8	2.2
100	10	M	100kHz, 0.1V	0.101	35	2.4	2
150	15	M	100kHz, 0.1V	0.15	25	2	1.5
220	22	M	100kHz, 0.1V	0.207	19	1.6	1.3
330	33	M	100kHz, 0.1V	0.334	15	1.4	1.1
470	47	M	100kHz, 0.1V	0.472	13	1	0.8
680	68	M	100kHz, 0.1V	0.66	10	0.9	0.7
101	100	M	100kHz, 0.1V	1.11	7	0.8	0.6
151	150	M	100kHz, 0.1V	1.55	6	0.6	0.5
221	220	M	100kHz, 0.1V	2	5	0.5	0.37
102	1000	M	100kHz, 0.1V	8.3	2	0.32	0.17

### MCPS5022 Type

Codes	L (μH)	Tolerance	Test Condition	DCR (Ω) Maximum	SRF Reference (MHz)	IDC (A) Maximum	I rms (A) Maximum
100	10	M	100kHz, 0.1V	0.04	30	8	3.9
150	15	M	100kHz, 0.1V	0.048	20	7	3.4
220	22	M	100kHz, 0.1V	0.059	18	6	3.1
330	33	M	100kHz, 0.1V	0.075	14	5	2.8

Codes	L (μH)	Tolerance	Test Condition	DCR (Ω) Maximum	SRF Reference (MHz)	IDC (A) Maximum	I rms (A) Maximum
470	47	M	100kHz, 0.1V	0.097	10	4	2.4
680	68	M	100kHz, 0.1V	0.138	9	3	2
101	100	M	100kHz, 0.1V	0.207	7	2.4	1.7
151	150	M	100kHz, 0.1V	0.293	6	2.1	1.3
221	220	M	100kHz, 0.1V	0.47	5	1.9	1.1
331	330	M	100kHz, 0.1V	0.78	4	1.1	0.86
471	470	M	100kHz, 0.1V	1.08	3	1.1	0.73
681	680	M	100kHz, 0.1V	1.4	2.5	0.96	0.64
102	1000	M	100kHz, 0.1V	2.01	2	0.8	0.53

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.