

TECHNICAL DATA SHEET

PRO-ELEC

CAT 5E UTP CABLE LSZH CB21175

**RoHS
Compliant**

Part Number	Description	Packaging
CB21175	CAT 5E UTP CABLE VIOLET 305M	305M pull box

ISO/IEC11801 Class D Permanent Link, ANSI/TIA/-568-C.2 Category 5E EC60332-1-2

Construction		
Conductor	Material	Solid Bare Copper
	Nom O.D. (mm):	0.48±0.005mm
Insulation	Material	HDPE
	Diameter:	0.85±0.02mm
	Colour	Pair 1: Blue and White/Blue
		Pair 2: Orange and White/Orange
		Pair 3: Green and White/Green
Rip cord:	Colour	Pair 4: Brown and White/Brown
Sheath	Material	LSZH
	Thickness	0.50±0.05 mm
	External O.D.	5.0±0.3 mm
	Colour:	Violet

Characteristics at 20°C

Sheath Physical Properties	Before Aging	Tensile Strength (Mpa): ≥10.0
		Elongation (%): ≥120
	Aging Period (°C×hrs):	100°C×24h×7d
	After Aging	Tensile Strength (Mpa): ≥8.0
		Elongation (%): ≥100
Electrical Characteristics	Cold bend (-20±2°C×4h)	No visible cracks
	1.0-100.0MHz, impedance (Ω)	100±15
	1.0-100.0MHz, Delay Skew (ns/100m)	≤45
	DC Resistance (Ω/100m)	≤10.6



Important Notice : This data sheet and its contents (the "Information") belong to pro-ELEC. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-ELEC assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-ELEC was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-ELEC's liability for death or personal injury resulting from its negligence.

PRO-ELEC

TECHNICAL DATA SHEET

PRO-ELEC

Technical Performance (FLUKE Link 90m±3m):

Frequency	RL	ATT	NEXT	DELAY	PSNEXT	ELFEXT	PSELFEX
MHz	≥dB	≤dB	≥dB	≤ns	≥dB	≥dB	≥dTB
1	20.0	2.0	65.3	570.00	62.3	64.0	61.0
4	23.0	4.1	56.3	552.00	53.3	52.0	49.0
8	24.5	5.8	51.8	546.73	48.8	45.9	42.9
10	25.0	6.5	50.3	545.38	47.3	44.0	41.0
16	25.0	8.2	47.2	543.00	44.4	39.9	36.9
20	25.0	9.3	45.8	542.05	42.8	38.0	35.0
25	24.3	10.4	44.3	541.20	41.3	35.8	33.0
31.25	23.6	11.7	42.9	540.44	39.9	34.1	31.1
62.5	21.5	17.0	38.4	538.55	35.4	28.1	25.1
100	20.1	22.0	35.3	537.60	32.3	24.0	21.0

PRO-ELEC