


S1 Twin Relay Series

UL Approved* Miniature High Voltage Relay

- Single-in-line package
- 1.5kV Isolation Voltage across contacts
- Isolation Voltage 1.5kV contact to coil
- 1.3A carry current
- Up to 1000V switching voltage



Actual device may differ

The S1-TWIN switch relay series is a miniature high voltage single-in-line reed relay with two reed switches for applications where space saving is a prime consideration.

The coil pins are positioned near the centre of the relay while the contact pins are near the ends to give improved isolation between the high voltage contacts and the low voltage coil.

Please refer to this document for circuit design notes:-
<http://www.cynergy3.com/blog/application-notes-reed-relays-0>

Custom versions can be designed for particular applications. Please contact Cynergy3 with your requirements.

*Consult factory for UL ratings

These products have been UL approved for use as per pollution degree 2 classification. If you require further information as to how this may affect product usage, please contact sales@cynergy3.com.



Made in the UK

Cynergy3 Components Ltd.
 7 Cobham Road
 Ferndown Industrial Estate
 Wimborne, Dorset BH21 7PE
 Telephone +44 (0) 1202 897969
 Email:sales@cynergy3.com

ISO9001 CERTIFIED

S1-Twin Series 2019




Contact Specification	Conditions	
Switch action		2 x SPST (Form A)
Material		Rhodium
Isolation across contacts	kV DC or AC peak	1.5
Switching Power Max.	W	10
Switching Voltage Max.	Vdc	1000
Switching Current Max.	Adc	0.5
Carry Current Max	Adc	1.3
Capacitance across contacts	pF coil to screen grounded	0.2E-12
Lifetime operations	dry switching	(TBC)
Contact Resistance	mΩmax	100
Insulation Resistance	Ωmin (typical)	(TBC)

Coil Specification (@ 20°C)		5V coil	12V coil	24V coil
Must Operate Voltage V	DC	3.75	9	18
Must Release Voltage V	DC	0.5	1.2	2.4
Operate Time(max)	ms diode fitted	0.75	0.75	0.75
Release Time (max)	ms diode fitted	0.3	0.3	0.3
Resistance	Ω (± 10%)	250	780	2000


Relay Specification		
Isolation contact/coil	kV DC	1.5
Insulation resistance contact to all terminals	Ωmin (typical)	TBC

Environmental		
Operating Temp range	°C	-40 to +85
Storage Temp range	°C	-40 to +100

Part Numbering System (e.g. S1-05-2ADM)



Mechanical Dimensions



www.cynergy3.com