


TECHNICAL DATA SHEET

PRO-ELEC

Cable Glands - Metal CB21887 - 898

**RoHS
Compliant**

Part No.	Thread Size mm	Cable Range	Thread OD L2 (mm)	Thread Length L1 (mm)	Spanner Size mm
CB21887	PG7	4-7	12.5	6	14
CB21888	PG9	5-8	15.2	7	18
CB21889	PG11	6-10	18.6	8	19
CB21890	PG13.5	8-12	20.4	9	22
CB21891	PG16	11-14	22.5	9	24
CB21892	PG21	14-18	28.3	9	30
CB21893	PG29	18-25	37	10	40
CB21894	M12x1.5	4-7	12	6	14
CB21895	M16x1.5	5-8	16	7	18
CB21896	M20x1.5	8-12	20	8	22
CB21897	M25x1.5	11-14	25	9	27/24
CB21898	M32x1.5	16-22	32	11	34
Material(A,C,F):	Nickel plated brass				
Material(B,E):	NBR				
Material (D)	Nylon PA66				
Protection Degree:	IP68 with ability to resist salt, acid, alkali, alcohol, grease and general solvents.				
Working Temperature	-20 to 80°C				



Important Notice : This data sheet and its contents (the "Information") belong to pro-ELEC. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-ELEC assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-ELEC was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-ELEC's liability for death or personal injury resulting from its negligence.

PRO-ELEC