



SAFETY DATA SHEET

according to Regulation (EU) 2015/830

Page 1/6

Q-No Clean Rework wand

Revision 0

Revision date 2017-08-31

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name	Q-No Clean Rework wand
--------------	------------------------

1.2. Relevant identified uses of the substance or mixture and uses advised against

Description	Soldering.
-------------	------------

1.3. Details of the supplier of the safety data sheet

Company	Qualitek Europe Ltd
Address	Unit 9 Apex Court Bassendale Road Bromborough Wirral CH62 3RE
Web	www.qualitek.com
Telephone	+ 44(0)151 334 0888
Fax	+ 44(0)151 334 1408
Email address of the competent person	sales@qualitek-europe.com

1.4. Emergency telephone number



Emergency telephone number	+ 44(0)151 334 0888 9.00 am - 5.00 pm Mon -Fri
----------------------------	---

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

2.1.2. Classification - EC 1272/2008	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336;
--------------------------------------	--

2.2. Label elements

Hazard pictograms	 
Signal Word	Danger
Hazard Statement	Flam. Liq. 2: H225 - Highly flammable liquid and vapour. Eye Irrit. 2: H319 - Causes serious eye irritation. STOT SE 3: H336 - May cause drowsiness or dizziness.
Precautionary Statement: Prevention	P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P261 - Avoid breathing dust/fume/gas/mist/vapours/spray. P264 - Wash thoroughly after handling. P280 - Wear protective gloves/protective clothing/eye protection/face protection.

Q-No Clean Rework wand

Revision 0

Revision date 2017-08-31

2.2. Label elements

Precautionary Statement: Response	P304+P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing. P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P312 - Call a POISON CENTER/doctor/ /if you feel unwell. P337+P313 - If eye irritation persists: Get medical advice/attention.
Precautionary Statement: Storage	P403+P233 - Store in a well-ventilated place. Keep container tightly closed. P405 - Store locked up.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

EC 1272/2008

Chemical Name	Index No.	CAS No.	EC No.	REACH Registration Number	Conc. (%w/w)	Classification
Isopropanol (Propan-2-ol)	603-117-00-0	67-63-0	200-661-7	01-2119457558-25	90 - 100%	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336;
Other(not classified)					1 - 10%	STOT SE 3: H335;

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation	Irritating to respiratory system. Inhalation may cause coughing, tightness of the chest and irritation of the respiratory system. Move the exposed person to fresh air. Seek medical attention.
Eye contact	Irritating to eyes. Rinse immediately with plenty of water for 15 minutes holding the eyelids open. Seek medical attention if irritation or symptoms persist.
Skin contact	Irritating to skin. Wash off immediately with plenty of soap and water. Remove contaminated clothing. Seek medical attention if irritation or symptoms persist.
Ingestion	Ingestion may cause nausea and vomiting. Seek medical attention if irritation or symptoms persist. DO NOT INDUCE VOMITING.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation	May cause irritation to respiratory system.
Eye contact	May cause irritation to eyes.
Skin contact	May cause dermatitis.
Ingestion	Seek medical attention.

4.3. Indication of any immediate medical attention and special treatment needed

Inhalation	Coughing, difficulty in breathing and in severe cases, loss of consciousness.
Eye contact	Rinse immediately with plenty of water for 15 minutes holding the eyelids open.
Skin contact	Avoid prolonged or repeated exposure.
Ingestion	DO NOT INDUCE VOMITING.

SECTION 5: Firefighting measures

5.1. Extinguishing media

	Carbon oxides. Alcohol resistant foam.
--	--

5.2. Special hazards arising from the substance or mixture

	Burning produces irritating, toxic and obnoxious fumes. Vapour may travel considerable distance to source of ignition and flash back.
--	---

5.3. Advice for firefighters

	Self-contained breathing apparatus. Wear protective clothing.
--	---

SECTION 6: Accidental release measures

Q-No Clean Rework wand

Revision 0

Revision date 2017-08-31

6.1. Personal precautions, protective equipment and emergency procedures

	Ensure adequate ventilation of the working area. Wear suitable protective equipment. Eliminate all sources of ignition. Evacuate personnel to a safe area.
--	--

6.2. Environmental precautions

	Do not allow product to enter drains. Prevent further spillage if safe.
--	---

6.3. Methods and material for containment and cleaning up

	Absorb with inert, absorbent material. Sweep up. Transfer to suitable, labelled containers for disposal. Clean spillage area thoroughly with plenty of water.
--	---

SECTION 7: Handling and storage

7.1. Precautions for safe handling

	Avoid contact with eyes and skin. Ensure adequate ventilation of the working area. Use explosion proof equipment. Keep away from sources of ignition - No smoking.
--	--

7.2. Conditions for safe storage, including any incompatibilities

	Keep in a cool, dry, well ventilated area. Keep containers tightly closed. Store in correctly labelled containers.
--	--

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1. Exposure Limit Values

Isopropanol (Propan-2-ol)	WEL 8-hr limit ppm: 400	WEL 8-hr limit mg/m3: 999
	WEL 15 min limit ppm: 500	WEL 15 min limit mg/m3: 1250
	WEL 8-hr limit mg/m3 total - inhalable dust:	WEL 15 min limit mg/m3 total - inhalable dust:
	WEL 8-hr limit mg/m3 total - respirable dust:	WEL 15 min limit mg/m3 total - respirable dust:

8.2. Exposure controls

8.2.1. Appropriate engineering controls	Ensure adequate ventilation of the working area.
8.2.2. Individual protection measures	Wear chemical protective clothing.
Eye / face protection	Approved safety goggles.
Skin protection - Handprotection	Chemical resistant gloves (PVC).
Respiratory protection	Wear suitable respiratory equipment when necessary.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Q-No Clean Rework wand

Revision 0

Revision date 2017-08-31

9.1. Information on basic physical and chemical properties

Appearance	Liquid
Colour	Clear
Odour	Alcoholic
Melting point	Not applicable.
Freezing Point	Not applicable.
Initial boiling point	81 - 83 °C
Flash point	12 °C
Evaporation rate	1.7 g/min
Flammability (solid, gas)	Not applicable.
Upper Explosive Limit	12 %
Lower Explosive Limit	2 %
Vapour pressure	43 Pa
Vapour density	2.1 g/cm ³
Fat Solubility	Not applicable.
Partition coefficient (n-octanol/water)	0.05 log P oct/wat
Autoignition temperature	425 °C
Explosive properties	Not relevant
Oxidising properties	No data available
Solubility	Miscible in water

SECTION 10: Stability and reactivity

10.2. Chemical stability

	Stable under normal conditions.
--	---------------------------------

10.3. Possibility of hazardous reactions

	Oxidising agents.
--	-------------------

10.4. Conditions to avoid

	Heat, sparks and open flames.
--	-------------------------------

SECTION 11: Toxicological information

11.1.4. Toxicological Information

Isopropanol	Dermal Rat LD50: 13900 mg/kg Dermal Rabbit LD50: 12870 mg/kg	Oral Rat LD50: 5840 mg/kg Inhalation Rat LC50/4 h: 72.6 mg/L
-------------	---	---

SECTION 12: Ecological information

12.1. Toxicity

Isopropanol	Algae EC50/120h: >1000 mg/L Lepomis_Macrochirus LC50/96h: >14000000 ug/L	Algae EC50/72h: >1000 mg/L
-------------	---	----------------------------

SECTION 13: Disposal considerations

General information

	Dispose of in compliance with all local and national regulations.
--	---

SECTION 14: Transport information

Hazard pictograms

Q-No Clean Rework wand

Revision 0

Revision date 2017-08-31

Hazard pictograms



14.1. UN number

UN1219

14.2. UN proper shipping name

ISOPROPANOL

14.3. Transport hazard class(es)

ADR/RID	3
Subsidiary risk	-
IMDG	3
Subsidiary risk	-
IATA	3
Subsidiary risk	-

14.4. Packing group

Packing group	II
---------------	----

14.5. Environmental hazards

Environmental hazards	No
Marine pollutant	No

ADR/RID

Hazard ID	33
Tunnel Category	(D/E)

IMDG

EmS Code	F-E S-D
----------	---------

IATA

Packing Instruction (Cargo)	364
Maximum quantity	60 L
Packing Instruction (Passenger)	353
Maximum quantity	5 L

Further information

The product is not classified as dangerous for carriage.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Regulations	REGULATION (EC) No 1907/2006 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC.
-------------	---

SECTION 16: Other information

Other information

Q-No Clean Rework wand

Revision 0

Revision date 2017-08-31

Other information

Text of Hazard Statements in Section 3	Flam. Liq. 2: H225 - Highly flammable liquid and vapour. Eye Irrit. 2: H319 - Causes serious eye irritation. STOT SE 3: H336 - May cause drowsiness or dizziness. STOT SE 3: H335 - May cause respiratory irritation.
---	--

Further information

	The information supplied in this Safety Data Sheet is designed only as guidance for the safe use, storage and handling of the product. This information is correct to the best of our knowledge and belief at the date of publication however no guarantee is made to its accuracy. This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any other process.
--	--