


| | | | |
|----------------------|----------|------------------|------------|
| MCCOG128064B12W-SPR | 128 x 64 | N/A | LCD Module |
| Specification | | | |
| Version: 1 | | Date: 31/10/2016 | |
| Revision | | | |
| | | | |

| Display Features | |  | |
|-----------------------|-----------------------|--|------------------|
| Resolution | 128 x 64 | | |
| Appearance | Black on Yellow/Green | | |
| Logic Voltage | 3.3V | | |
| Interface | Parallel / SPI | | |
| Font Set | N/A | | |
| Display Mode | Reflective | | |
| LC Type | STN | | |
| Module Size | 54.60 x 42.20 x 1.905 | | |
| Operating Temperature | -20°C ~ +70°C | | |
| Construction | COG | | |
| LED Backlight | --- | Box Quantity | Weight / Display |
| | | --- | --- |

* - For full design functionality, please use this specification in conjunction with the ST7565P specification. (Provided Separately)


| Display Accessories | |
|---------------------|--|
| Part Number | Description |
| MCIB-12 | UNO 32 Breakout Board with SD Card and LED BKL driver. |
| MPBV-7 | 30-Way FFC to Cable and Wires 0.5mm Pitch. |
| | |

| Optional Variants | |
|---|---------|
| Appearances | Voltage |
| White on Blue Black on White Black on RGB | |



Mechanical Specifications

| | | | | | |
|--------------|--|----------|--------------|--------------|----------|
| Module Size | 54.60 x 42.20 x 1.905 (Without Backlight) | | | W x H x D mm | |
| Viewing Area | 50.60 x 31.00 | W x H mm | Hole-to-Hole | --- | W x H mm |
| Dot Size | --- | W x H mm | Dot Pitch | --- | W x H mm |



| | | | |
|----------------------|------------------|-----|------------|
| MCCOG128064B12W-SPR | 128 x 64 | N/A | LCD Module |
| Specification | | | |
| Version: 1 | Date: 31/10/2016 | | |
| Revision | | | |
| | | | |



Pin layout

| Pin | Symbol | Description | Remarks |
|-----|-----------|--|---------|
| 1 | P/S | P/S = H: Parallel Data I/O P/S = L: Serial Data Input | |
| 2 | C86 | MPU Interface Selection Pin | |
| 3 | V0 | Multi-Level power supply for LCD. Voltage applied is determined by LC cell, changed through resistive voltage divided or changing impedance using OP. AMP. Levels determined on VSS must maintain magnitudes shown: $V0 \geq V1 \geq V2 \geq V3 \geq V4 \geq VSS$ | |
| 4 | V1 | | |
| 5 | V2 | | |
| 6 | V3 | | |
| 7 | V4 | | |
| 8 | C2- | DC/DC Converter. Capacitor between this terminal and CAP2P terminal. | |
| 9 | C2+ | DC/DC Converter. Capacitor between this terminal and CAP2N terminal. | |
| 10 | C1+ | DC/DC Converter. Capacitor between this terminal and CAP1N terminal. | |
| 11 | C1- | DC/DC Converter. Capacitor between this terminal and CAP1P terminal. | |
| 12 | C3+ | DC/DC Converter. Capacitor between this terminal and CAP1N terminal. | |
| 13 | VOUT | Voltage Converter I/O | |
| 14 | VSS | Ground | |
| 15 | VDD | Power Supply | |
| 16 | D7 | 8-Bit bi-directional data bus, connect to 8-bit or 16-bit standard MPU data bus. SPI-4 is selected P/S = L D7 Serial data input (SI); D6 Serial Clock Input (SCL). D0~D5 connected to VDD or floating. When chip select not active, D0~D7 set to high impedance. | |
| 17 | D6 | | |
| 18 | D5 | | |
| 19 | D4 | | |
| 20 | D3 | | |
| 21 | D2 | | |
| 22 | D1 | | |
| 23 | D0 | | |
| 24 | E (/RD) | When connected to 8080MPU, Pin treated as the "/RD" signal of the 8080MPU and is LOW-active. Data bus output status when signal is "L". Connect 6800 MPU, pin treated as "E" signal of 6800 MPU, and is HIGH-active. | |
| 25 | R/W (/WR) | When connected to 8080MPU, Pin treated as the "/WR" signal of the 8080MPU and is LOW-active. Connect 6800 MPU, pin treated as "R/W" signal of 6800 MPU, decides access type: R/W = H: Read R/W = L: Write. | |
| 26 | D/C | Determines whether data bits are data or command. | |
| 27 | /CS1 | Chip Select. | |
| 28 | /RES | /Res is "L", register settings initialised. Reset operation is performed by the /RES signal Level. | |

| | | | |
|----------------------|----------|------------------|------------|
| MCCOG128064B12W-SPR | 128 x 64 | N/A | LCD Module |
| Specification | | | |
| Version: 1 | | Date: 31/10/2016 | |
| Revision | | | |
| | | | |



| Absolute Maximums Ratings | | | | | |
|---------------------------|-----------------|---------|---------|---------|------|
| Item | Symbol | Minimum | Typical | Maximum | Unit |
| Power Supply Voltage | V0, VOUT | -0.3 | --- | 14.5 | V |
| Power Supply Voltage | V1,V2,V3,V4 | -0.3 | --- | V0+0.3 | V |
| Power Supply Voltage | VDD | -0.3 | --- | 3.6 | V |
| Operating Temperature | T _{OP} | -20°C | --- | 70°C | °C |
| Storage temperature | T _{ST} | -30°C | --- | 80°C | °C |

| Electronic Characteristics | | | | | | |
|----------------------------|-----------------------------------|-----------------------|---------|---------|---------|------|
| Item | Symbol | Condition | Minimum | Typical | Maximum | Unit |
| --- | --- | --- | --- | --- | --- | --- |
| --- | --- | --- | --- | --- | --- | --- |
| --- | --- | --- | --- | --- | --- | --- |
| --- | --- | --- | --- | --- | --- | V |
| Supply Voltage Logic | V _{DD} - V _{SS} | --- | 3.20 | 3.30 | 3.40 | V |
| Supply Voltage LCD | V _{DD} - V ₀ | T _a =25°C | 8.60 | 8.80 | 9.00 | V |
| Supply Current | I _{DD} | V _{DD} =3.3V | --- | 0.10 | --- | mA |

| LCD Characteristics | | | | | | |
|------------------------------|---------------------------------|-----------|---------|---------|---------|--------|
| For STN/FSTN LCD Panel Types | | | | | | |
| Item | Symbol | Condition | Minimum | Typical | Maximum | Unit |
| Viewing Angle | Φ ₂ - Φ ₁ | CR ≥ 2 | --- | --- | 45 | ψ=180° |
| | Θ | --- | --- | | | |
| Contrast Ratio | CR | --- | 3 | --- | --- | --- |
| Response Time (Rise) | TR | --- | --- | --- | 250 | ms |
| Response Time (Fall) | TF | --- | --- | --- | 250 | ms |

| | | | |
|----------------------|----------|------------------|------------|
| MCCOG128064B12W-SPR | 128 x 64 | N/A | LCD Module |
| Specification | | | |
| Version: 1 | | Date: 31/10/2016 | |
| Revision | | | |
| | | | |

