



CARBON™ SWING-OUT WALL MOUNT ENCLOSURE

CR12U51001

Swing-out wall mount enclosure safeguards 12U of 19" rack equipment

The CR12U51001 is designed for use in network closets, classrooms and other locations. It houses network switches and patch panels up to 22 inches deep. This enclosure features convenient top panel cable access openings, perforated doors and side panels for efficient airflow, adjustable rack angles, and square and threaded mounting holes. The CR12U51001 ships fully assembled for quick deployment, and can be customized with compatible accessories. It is covered by a 5-year limited warranty.

FEATURES

- Rack Type: Swing-out Wall Mount Enclosure
- Height: 12U
- Stationary Capacity: 132 lbs
- Max. Mounting Depth: 18.2"
- Mounting Hole Types: Square and Threaded
- Warranty: 5 Years

TYPICAL APPLICATIONS

- Network Closets
- Retail Locations
- Back Office
- Classrooms



SPECIFICATIONS

PHYSICAL		PHYSICAL - CONT.	
Rack Height	12U	Weight Capacity - stationary load (lbs)	132.3
Color	Black RAL 9005 powder coat paint	Weight Capacity - stationary load (kg)	60
Door Type	Hex Perforated Metal Door	Factory Default Mounting Depth (in)	13.2
Wall Mount Rear Frame	Swing Out	Factory Default Mounting Depth (mm)	336
Rack Angle Mounting Hole Type	Square and #12-24 Mounting Hole	Cable Access Opening Dimensions (in)	9.8 x 2.2

CARBON™ SWING-OUT WALL MOUNT ENCLOSURE

CR12U51001



SPECIFICATIONS CONT.

PHYSICAL - CONT.

Cable Access Opening Dimensions (mm)	250 x 56
Max. Mounting Depth (in)	18.2
Max. Mounting Depth (mm)	462
Min. Mounting Depth (in)	1.9
Min. Mounting Depth (mm)	47
Dimensions (WxHxD in.)	23.6 x 25.1 x 23.6
Dimensions (WxHxD mm)	600 x 637 x 600
Net Weight (lbs)	60.2
Net Weight (kg)	27.3
Shipping Dimensions - WxHxD (in)	26.18 x 27.8 x 26.18
Shipping Dimensions - WxHxD (mm)	665 x 705 x 665
Shipping Weight (lbs)	67.7
Shipping Weight (kg)	30.7

SPECIAL FEATURES

Numbered Rack Units	Yes
Rolling Casters	Optional
Removable Door and Side Panels	Yes
Reversible Front Door	Yes
Lockable Door and Side Panels	Yes, keyed alike
Ventilation	Perforated Door and Side Panels with Ventilated Top and Bottom
Cable Access	Top and Bottom Openings
PE Grounding Point	Yes

ENVIRONMENTAL

Protection Class	IP20
------------------	------

CERTIFICATIONS

Certifications	CE, RoHS
Approvals	DIN41491, DIN41494, EIA/ECA-310-E, IEC 60297-3-100

WARRANTY

Product Warranty	5 Years Limited
------------------	-----------------