

PRODUCT DATA SHEET

EVERBUILD® Weather Mate®

AN ADVANCED GAP FILLER AND ADHESIVE FOR THE ULTIMATE ALL WEATHER APPLICATIONS.

PRODUCT DESCRIPTION

EVERBUILD® Weather Mate® is a multi-use elastic filler that can be applied in wet weather and to wet surfaces, even under water, remaining permanently flexible. Intended for external use only it can be over-painted with most paints and woodstains when cured. Adheres to most common surfaces.

USES

- For all roofline applications.
- Adheres to problematic surfaces such as bitumen, asphalt, lead and galvanized steel.
- Perimeter gap filling around window and door frames; ideal for timber frames where woodstaining is required.
- For jointing all types of guttering.
- Filling cracks in stone tiles/slates etc.
- For all external weatherproofing applications.
- For filling gaps between metal and composite roof and wall panels to form an effective lap joint bond.
- For remedial weather proofing over all sealants, putties and mastics.
- General industrial metal panel bonding and gap filling.

CHARACTERISTICS / ADVANTAGES

- Can be applied in all weathers.
- Sticks to wet surfaces.
- Resists all weather conditions.
- Permanently flexible.
- Can be used in conjunction with Bitumen and asphalt.

Shrinkage _____ ca. 25%

PRODUCT INFORMATION

Packaging	295ml cartridge
Colour	White, Translucent and Black
Shelf Life	Use within two years.
Storage Conditions	Store in cool (5 - 25°C) dry conditions with good ventilation and away from sources of ignition.
Density	0.9-1.0 g/cm ³

TECHNICAL INFORMATION

Shore A Hardness	22
Elongation at Break	350% DIN53504
Service Temperature	-25°C to + 95°C
Joint Design	Joint Ratio - Maximum depth 50% of joint width Minimum Joint Width - 5mm Maximum Joint Width - 35mm

APPLICATION INFORMATION

Ambient Air Temperature	+5°C to + 50°C
Curing Time	2mm per 24hours
Skin Time	15mins at 20°C

APPLICATION INSTRUCTIONS

SUBSTRATE PREPARATION

All surfaces must be clean and dust free. All loose or flaking surface coatings should be removed before application. Glass, metal and aluminium should be cleaned with a solvent cleaner prior to application for optimum adhesion.

APPLICATION METHOD / TOOLS

Cut the tip of the cartridge taking care not to damage the thread. Apply nozzle and cut cleanly at an angle of 45° with an opening slightly larger than the gap to be sealed. Apply using a standard sealant gun. Best results will be obtained by keeping an even pressure on the gun trigger and keeping the gun at a constant angle to the surface being sealed. Always tool down immediately following application using a spatula or piece of wood wetted with a soap and water solution. When applied to wet surfaces tooling down is essential to ensure a proper bond with the surface is formed. The product is tack free after 10-15 minutes, and should be allowed to cure for 24 hours before painting. Clean tools with white spirits.

CLEANING OF TOOLS

For uncured product use Everbuild White Spirit, if cured this should be removed mechanically.

LIMITATIONS

- DO NOT USE INTERNALLY – For exterior use only.
- Do not use in food preparation areas.
- Do not use in aquarium manufacture.
- When used over bitumen or Asphalt, some staining may be noticeable on white and transparent grades. This will not affect the technical performance of the product.
- It is the user's responsibility to determine suitability for use. If in doubt, please contact Technical Services Department for advice.

VALUE BASE

All technical data stated in this Data Sheet are based on laboratory tests. Actual measured data may vary due to circumstances beyond our control.

LOCAL RESTRICTIONS

Note that as a result of specific local regulations the declared data and recommended uses for this product may vary from country to country. Consult the local Product Data Sheet for the exact product data and uses.

ECOLOGY, HEALTH AND SAFETY

For information and advice on the safe handling, storage and disposal of chemical products, users shall refer to the most recent Safety Data Sheet (SDS) containing physical, ecological, toxicological and other safety-related data.

LEGAL NOTES

The information, and, in particular, the recommendations relating to the application and end-use of Sika products, are given in good faith based on Sika's current knowledge and experience of the products when properly stored, handled and applied under normal conditions in accordance with Sika's recommendations. In practice, the differences in materials, substrates and actual site conditions are such that no warranty in respect of merchantability or of fitness for a particular purpose, nor any liability arising out of any legal relationship whatsoever, can be inferred either from this information, or from any written recommendations, or from any other advice offered. The user of the product must test the product's suitability for the intended application and purpose. Sika reserves the right to change the properties of its products. The proprietary rights of third parties must be observed. All orders are accepted subject to our current terms of sale and delivery. Users must always refer to the most recent issue of the local Product Data Sheet for the product concerned, copies of which will be supplied on request.

EVERBUILD BUILDING PRODUCTS LTD

Site 41, Knowsthorpe Way
Cross Green Industrial Estate
Leeds, LS9 0SW
Tel: 0113 240 3456
Web: www.everbuild.co.uk
Twitter: @everbuild

SIKA LIMITED

Watchmead
Welwyn Garden City
Hertfordshire, AL7 1BQ
Tel: 01707 394444
Web: www.sika.co.uk
Twitter: @SikaLimited

SIKA IRELAND LIMITED

Ballymun Industrial Estate
Ballymun
Dublin 11, Ireland
Tel: +353 1 862 0709
Web: www.sika.ie
Twitter: @SikaIreland

EVERBUILDWeatherMate-en-GBEVER-(07-2018)-2-1.pdf

Product Data Sheet
EVERBUILD® Weather Mate®
July 2018, Version 02.01
020511080000000026



BUILDING TRUST

