

Power distribution board - EM-CPS-225 - 1002634

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Modular power distribution board with CrossLink[®] interface, 125 A, 3-pos., touch-proof and protection against polarity reversal, width: 225 mm

Your advantages

- ✓ Protection against polarity reversal - phase rotation not possible
- ✓ Quick, complete out-of-the-box system
- ✓ Compact design compared to conventional power distribution

RoHS

COMPLETE RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 468228
GTIN	4055626468228
Weight per Piece (excluding packing)	797.100 g
Custom tariff number	85369095
Country of origin	Germany

Technical data

Note

Type of note	Assembly instruction:
--------------	-----------------------

Dimensions

Width	225 mm
Height	160 mm
Depth	45.1 mm

Ambient conditions

Degree of protection	IP20
----------------------	------

General

Rated voltage	600 V DC (IEC)
---------------	----------------

Power distribution board - EM-CPS-225 - 1002634

Technical data

General

	600 V AC/DC (UL)
Rated current	125 A (IEC)
	100 A (UL)
Rated peak withstand current	25 kA
Degree of protection	IP20

Standards and Regulations

Rated surge voltage	6 kV
---------------------	------

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27371392
eCl@ss 4.0	27378000
eCl@ss 4.1	27378000
eCl@ss 5.0	27379100
eCl@ss 5.1	27379100
eCl@ss 6.0	27379200
eCl@ss 7.0	27379201
eCl@ss 8.0	27379201
eCl@ss 9.0	27379201

ETIM

ETIM 4.0	EC002498
ETIM 5.0	EC002498
ETIM 6.0	EC002498
ETIM 7.0	EC002498

Approvals

Approvals

Approvals

UL Listed / cUL Listed / EAC / EAC / cULus Listed

Ex Approvals

Power distribution board - EM-CPS-225 - 1002634

Approvals

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 123528
cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 123528
EAC			RU C- DE.A*30.B.01742
EAC			RU*DE*08.B.01841/19
cULus Listed			

Accessories

Accessories

Adapter

Adapter - EM-CPS-DA-22,5F/16A - 1002668



Device adapter with fuse holder for 16 A fuse (10x38/Class CC), CrossLink[®] interface and fixed DIN rail

Adapter - EM-CPS-DA-45S/16A - 1003291



Standard device adapter with CrossLink[®] interface and fixed DIN rail, rated current: 16 A

Power distribution board - EM-CPS-225 - 1002634

Accessories

Adapter - EM-CPS-DA-45S/32A - 1003292



Standard device adapter with CrossLink® interface and fixed DIN rail, rated current: 32 A

Adapter - EM-CPS-DA-45C/16A - 1002666



Comfort device adapter with CrossLink® interface and moveable DIN rail, rated current: 16 A

Adapter - EM-CPS-DA-45C/25A - 1002665



Comfort device adapter with CrossLink® interface and moveable DIN rail, rated current: 25 A

Adapter - EM-CPS-DA-45C/32A - 1002664



Comfort device adapter with CrossLink® interface and moveable DIN rail, rated current: 32 A

Adapter - EM-CPS-DA-45C/45A - 1003289



Comfort device adapter with CrossLink® interface and moveable DIN rail, rated current: 45 A

Power distribution board - EM-CPS-225 - 1002634

Accessories

Adapter - EM-CPS-DAE-45 - 1003293



Height extension for Comfort device adapter, width: 45 mm

Adapter - EM-CPS-DAES-45 - 1003294



Lateral extension of the height extension for Comfort device adapter, width: 45 mm

Adapter - EM-CPS-TS-45 - 1003295



Comfort DIN rail, additional DIN rail for Comfort device adapter

Adapter - EM-CPS-DHS-45 - 1003296



Siemens device mount, positioning element for Siemens S0 and S00 switching devices

Adapter - EM-CPS-DHE-45 - 1002663



Eaton device mount, positioning element for Eaton PKZ switching devices

Assembly adapter

Power distribution board - EM-CPS-225 - 1002634

Accessories

Connection module - EM-CPS-TB3/63A - 1002633



Connection module with integrated spring-loaded terminals for cables from 1.5 to 16 mm², 3-pos., maximum 63 A

Adapter - EM-CPS-PTFIX-135 - 1119251



Adapter rail for the CrossPowerSystem power distribution board with mounting for PTFIX distribution blocks

Adapter - EM-CPS-NS35-135 - 1119259



Adapter rail for the CrossPowerSystem power distribution board with integrated DIN rail for mounting distributor terminal blocks up to 35 mm²

Fuse

Fuse - FUSE-10X38-16A-GR - 2903126



Fuse, number: 10 Pcs., fuse type: Fuse (CC), nominal current: 16 A, tripping characteristic: super-fast blow (gR)

Switch disconnecter - EM-CPS-DISC-NH000/125A - 1151613



LV HRC fuse switch disconnecter size 000 with CrossLink[®]-interface, 125 A, connection bottom/top, with box terminals