

Key panel - BT05AM/792050 S00001 - 2400613

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Key panel with 7.6 cm/3" FSTN-display (Without touch technology), 5 grayscales, Arm9™, 200 MHz, 2x USB host 2.0, 1x COM (RS-232), 1x COM (RS-232/RS-485/TTY), 1 x Ethernet (10/100 Mbps), RJ45, Windows CE 5.0 and user software: TSvisRT. (bus system: without)

Similar figure

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 098449
GTIN	4055626098449
Weight per Piece (excluding packing)	500.000 g
Custom tariff number	84714100
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Outer dimensions: width, height, depth	120 mm x 168 mm x 5 mm (Dimensions of the front plate)
Installation dimensions: width, height, depth	112 mm x 160 mm x 55 mm (Mounting cutout, depth with bus if bus system present in the device)

Display

Display	7.6 cm/3" FSTN
Screen resolution	160 x 80 Pixel(s)
Touch technology	Without touch technology
Brightness	45 cd/m²
Backlighting	LED
Display backlight MTBF	50000 h

Key panel - BT05AM/792050 S00001 - 2400613

Technical data

Display

Colors	5 grayscales
Reading angle left	40 °
Reading angle right	40 °
Reading angle top	40 °
Reading angle bottom	40 °

Computer data

Processor	Arm9™, 200 MHz
Operating system	Windows® CE 5.0
User software	TSvisRT
RAM	64 MB SDRAM
	512 KB SRAM
Mass storage	NOR-Flash, 32 MB
Network	1 x Ethernet (10/100 Mbps), RJ45
Interfaces	2x USB Host 2.0
	1x COM (RS-232)
	1x COM (RS-232/RS-485/TTY)
Bus system	without
Optional interfaces	none
Realtime clock	Yes
Service life of battery	5 years (typical)

General

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated
Mounting type	Front installation
Weight	500 g

Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
	NEMA 4X
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	20 % ... 85 %
Vibration (operation)	1g, according to EN 60068-2-6
Shock	15g, according to IEC 60068-2-27

Device supply

Typical current consumption	0.25 A
Power supply unit	24 V DC ±20 %

Standards and Regulations

Shock	15g, according to IEC 60068-2-27
-------	----------------------------------

Key panel - BT05AM/792050 S00001 - 2400613

Technical data

Standards and Regulations

Vibration (operation)	1g, according to EN 60068-2-6
-----------------------	-------------------------------

Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 15;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	27330200
eCl@ss 4.1	27330200
eCl@ss 5.0	27330200
eCl@ss 5.1	27330200
eCl@ss 6.0	27242300
eCl@ss 7.0	27242302
eCl@ss 8.0	27242302
eCl@ss 9.0	27330201

ETIM

ETIM 5.0	EC001412
ETIM 6.0	EC001412
ETIM 7.0	EC001412

UNSPSC

UNSPSC 13.2	43211904
UNSPSC 18.0	43211904
UNSPSC 19.0	43211904
UNSPSC 20.0	43211904
UNSPSC 21.0	43211904

Approvals

Approvals

Approvals




UL Listed / cUL Listed / cULus Listed

Ex Approvals

Key panel - BT05AM/792050 S00001 - 2400613

Approvals

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 205795
cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 205795
cULus Listed			

Accessories

Accessories

Battery module

Battery / accumulator - HMI BATTERY - 2701383

Lithium battery



Mounting material

Mounting material - HMI SCB MOUNTING KIT 4 - 2701384



HMI mounting kit for installation on a front plate. The mounting kit includes 4 x mounting brackets, 4 x screw threads, and a hexagonal wrench.

Mounting material - HMI WALL MOUNTING KIT - 2701380



HMI mounting kit for panel installation. The mounting kit includes 2 spring clips.

Storage medium

Key panel - BT05AM/792050 S00001 - 2400613

Accessories

USB memory stick - USB FLASH DRIVE - 2402809



USB memory stick, 8 GB