

# Surface Mountable PTC Resettable Fuse

**multicomp** PRO

**RoHS  
Compliant**



## Specifications:

Applications	: All high-density boards.
Product Features	: Small surface mountable, solid state, faster time to trip than standard SMD devices, lower resistance than standard SMD devices.
Max. Voltage	: 6V to 60V.
Temperature Range	: -40°C to 85°C.

## Electrical Characteristics (23°C)

Hold Current	Trip Current	Rated Voltage	Max. Current	Typical Power	Max. Time to trip		Resistance		Part Number
					Current	Time	R <sub>Min</sub>	R <sub>1Max</sub>	
I <sub>H</sub> , A	I <sub>T</sub> , A	V <sub>MAX</sub> , V DC	I <sub>MAX</sub> , A	P <sub>D</sub> , W	Amperes	Seconds	Ω	Ω	
0.1	0.3	60	10	0.8	8	0.02	1.6	15	MC36204
0.35	0.7	16	40	0.8	8	0.1	0.32	1.5	MC36209
0.75	1.5	24	40	1	8	0.2	0.11	0.29	MC36218
0.75	1.5	33	40	1	8	0.2	0.11	0.4	MC36219
1.1	1.95	16	100	0.8	8	0.5	0.04	0.18	MC36224
1.1	2.2	24	100	1	8	0.5	0.06	0.2	MC36225
1.25	2.5	6	100	0.8	8	0.4	0.05	0.14	MC36226
1.25	2.5	6	100	0.8	8	0.4	0.05	0.14	MC36227
1.5	3	8	100	0.8	8	0.5	0.04	0.11	MC36228
1.5	3	12	100	1	8	0.5	0.04	0.11	MC36231
1.5	3	24	100	1	8	1.5	0.04	0.12	MC36232
1.6	3.2	8	100	0.8	8	0.5	0.03	0.1	MC36233
1.6	3.2	12	100	1	8	1	0.03	0.1	MC36234
1.6	3.2	16	100	1	8	1	0.03	0.1	MC36235
1.9	4.9	6	100	1	8	5	0.003	0.025	MC36237
2	3.5	8	100	1	8	2	0.02	0.07	MC36238
2.6	5	13.2	100	1.3	8	5	0.015	0.05	MC36242
2.6	5	16	100	1.3	8	5	0.015	0.05	MC36243
2.6	5	6	100	1	8	2.5	0.015	0.047	MC36244

I<sub>H</sub> = Hold current-maximum current at which the device will not trip at 23°C still air.

I<sub>T</sub> = Trip current-minimum current at which the device will always trip at 23°C still air.

V<sub>MAX</sub> = Maximum voltage device can withstand without damage at its rated current (I maximum).

I<sub>MAX</sub> = Maximum fault current device can withstand without damage at rated voltage (V maximum).

P<sub>D</sub> = Typical power dissipated-type amount of power dissipated by the device when in the tripped state in 23°C still air environment.

R<sub>Min</sub> = Minimum device resistance at 23°C prior to tripping.

R<sub>1Max</sub> = Maximum device resistance at 23°C measured 1 hour after tripping or reflow soldering of 260°C for 20 seconds.

Termination pad characteristics

Termination pad materials: Pure tin.


Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
Element14.com/multicomp-pro

**multicomp** PRO

# Surface Mountable PTC Resettable Fuse

**multicomp** PRO

## FSMD Product Dimensions (Millimetres)



## Dimensions Table


A		B		C		D		E		Figure	Part Number
Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.		
4.37	4.73	3.07	3.41	0.6	0.9	0.3	0.95	-	-	1	MC36204
4.37	4.73	3.07	3.41	0.4	0.7	0.3	0.95	-	-	1	MC36209
4.37	4.73	3.07	3.41	0.8	1.55	0.25	0.95	0.25	0.65	2	MC36218
4.37	4.73	3.07	3.41	0.8	1.55	0.25	0.95	0.25	0.65	2	MC36219
4.37	4.73	3.07	3.41	0.25	0.9	0.3	0.95	-	-	1	MC36224
4.37	4.73	3.07	3.41	0.8	1.3	0.25	0.95	0.25	0.65	2	MC36225
4.37	4.73	3.07	3.41	0.25	0.55	0.3	0.95	-	-	1	MC36226
4.37	4.73	3.07	3.41	0.25	0.55	0.3	0.95	-	-	1	MC36227
4.37	4.73	3.07	3.41	0.25	0.55	0.3	0.95	-	-	1	MC36228
4.37	4.73	3.07	3.41	0.6	1.1	0.25	0.95	0.25	0.65	2	MC36231
4.37	4.73	3.07	3.41	0.6	1.55	0.25	0.95	0.25	0.65	2	MC36232
4.37	4.73	3.07	3.41	0.25	0.9	0.3	0.95	-	-	1	MC36233
4.37	4.73	3.07	3.41	0.6	1.35	0.25	0.95	0.25	0.65	2	MC36234
4.37	4.73	3.07	3.41	0.6	1.35	0.25	0.95	0.25	0.65	2	MC36235
4.37	4.73	3.07	3.41	0.3	0.7	0.25	0.95	0.25	0.65	2	MC36237
4.37	4.73	3.07	3.41	0.55	1.2	0.25	0.95	0.25	0.65	2	MC36238
4.37	4.73	3.07	3.41	0.8	1.55	0.25	0.95	0.25	0.65	2	MC36242
4.37	4.73	3.07	3.41	0.8	1.55	0.25	0.95	0.25	0.65	2	MC36243
4.37	4.73	3.07	3.41	0.55	1.2	0.25	0.95	0.25	0.65	2	MC36244

Dimensions : Millimetres


# Surface Mountable PTC Resettable Fuse

**multicomp** PRO

## Thermal Derating Curve



## Typical Time-To-Trip at 23°C



## Material Specification

Terminal pad material : Pure tin.

Soldering characteristics : Meets EIA specification RS 186-9E, ANSI/J-std-002 category 3.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
Element14.com/multicomp-pro


**multicomp** PRO

# Surface Mountable PTC Resettable Fuse

**multicomp** PRO

## Pad Layouts Solder Reflow and Rework Recommendations

The dimension in the table below provide the recommended pad layout for each 1812 device.



### Pad Dimensions

Device	A Nominal	B Nominal	C Nominal
All 1812 Series	3.45	1.78	3.5

Dimensions : Millimetres

Profile Feature	Pb-Free Assembly
Average Ramp-Up Rate ( $T_s$ maximum to $T_P$ )	3°C/second maximum
Preheat:	
Temperature Minimum ( $T_s$ minimum)	150°C
Temperature Maximum ( $T_s$ maximum)	200°C
Time ( $t_s$ minimum to $t_s$ maximum)	60-180 seconds
Time maintained above:	
Temperature ( $T_L$ )	217°C
Time ( $t_L$ )	60-150 seconds
Peak/Classification Temperature ( $T_P$ ):	260°C
Time within 5°C of actual Peak:	
Temperature ( $t_p$ )	20-40 seconds
Ramp-Down Rate:	6°C/second maximum
Time 25°C to Peak Temperature:	8 minutes maximum

Note 1: All temperatures refer to of the package, measured on the package body surface.

## Solder reflow

Due to "Lead Free" nature, Temperature and Dwelling time for the soldering zone is higher than those for Regular. This may cause damage to other components.

1. Recommended max past thickness > 0.25mm.
2. Devices can be cleaned using standard methods and aqueous solvent.
3. Rework use standard industry practices.
4. Storage Environment : < 30°C/60%RH.

## Caution:

1. If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.
2. Devices are not designed to be wave soldered to the bottom side of the board.


Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
Element14.com/multicomp-pro

**multicomp** PRO

# Surface Mountable PTC Resettable Fuse

**multicomp** PRO

## Reflow Profile



## Part Number Table

Description	Part Number
Surface Mountable PTC Resettable Fuse	MC36204
	MC36209
	MC36218
	MC36219
	MC36224
	MC36225
	MC36226
	MC36227
	MC36228
	MC36231
	MC36232
	MC36233
	MC36234
	MC36235
	MC36237
	MC36238
	MC36242
MC36243	
MC36244	

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
Element14.com/multicomp-pro

**multicomp** PRO